Ortronics

Mighty Mo 20 Adjustable 4-Post Rack, 36"D adjustable, 8'H, 51 RU, Tapped Rails, White

Part No. MM20836ADJ12-W



Mighty Mo 20 4-post adjustable racks are allows all 4 mounting rails to be adjusted even after the rack has been fastened to the floor. Availble in depths of 30", 36" & 42" depths in both square hole cage nut styles or threaded rails. Front and rear waterfalls allow for equipment patching and server patching. All styles of Mighty Mo 20 vertical managers can be mounted front or rear and airflow baffles can be mounted to manage the airflow of side breathing equipment.

Features & Benefits

- Large selection of Channel and 4-Post racks
- ront and rear waterfalls allow for equipment patching and server patching
- Threaded hole and square hole punch available on all channel and 4 post racks
- Rack includes two packages of hook and loop D-style straps and 50 #12-24 cage nuts and screws, do not have to purchase as separate items; money saving
- All 4 mounting rails to be adjusted even after the rack has been fastened to the floor
- Static capacity 2,000 lbs
- Deeper waterfall for increased cable capacity

Specifications

General Info

Product Line	Ortronics	UPC Number	662875216780
Country Of Origin	United States		

Dimensions

Product Width US	23.75 in	Product Weight US	60.46 lb
Product Depth US	46.0 in	Product Height US	98.0 in

Additional Information

Product Environmental Profile	Yes