



## radiant Collection

**radiant® 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, NAFTA Compliant, Gray**  
Part No. 2097NAGRY



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection in the home, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. 20A outlets are ideal for use with larger appliances, as well as to meet regional requirements (Chicago, Canada). GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

### Features & Benefits

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI receptacles make it easier to fix trips with a reset button right on the device.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

NAFTA-Compliant devices are ideal for use on projects subject to the provisions of the Buy America Act.

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.

Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	GFCI, Indoor, Residential, Self-Test	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL	Warranty Type	1-Year Limited Warranty
Type	Outlet		

#### Dimensions

Product Width US	1.73 in	Product Depth US	1.13 in
------------------	---------	------------------	---------

---

Product Height US 4.2 in

---

**Listing Agencies / 3rd Party Agencies**

---

cULus Listed Yes

---

**Additional Information**

---

Product Environmental Profile Yes

---

**Technical Information**

---

Interrupt Rating 4 A Frequency Rating 60 Hz

---

Trip Range 5±1 mA Connection Back and Side Wire

---

Number of Gangs 1 Amperage 20 A

---

Number of Poles Double Pole Indoor/Outdoor Indoor

---

Mounting Type Box Voltage 125.0 V

---

Environmental Conditions 95% Humidity, UL 94 V2

---