



radiant Collection
radiant® Tamper-Resistant 20A Simplex Self-Test GFCI Receptacles with SafeLock® Protection, Black
Part No. 2097TRSGLBK



Specifically designed for use with large and/or stationary appliances like refrigerators, dishwashers and washing machines, this 20A GFCI outlet provides dedicated power and superior ground-fault protection while also limiting the nuisance tripping often caused by variable motor drives. Like all GFCI electrical outlets and plugs from the radiant® Collection, this device self-tests every three seconds for reliable safety and protection you can trust. Meeting the National Electrical Code requirements for ground fault protection in the home, GFCI wall outlets also make it easier to fix trips right where they happen – no more confusion or running to the breaker box. GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI receptacles make it easier to fix trips with a reset button right on the device	Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced
Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected	Includes green LED illuminated power indication to confirm the receptacle is energized
Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly	Replaces a traditional outlet easily, in as little as 10 minutes
Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect	More color options available to fit any style, including finishes to match current hardware and lighting trends
Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection	

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007381566
Country Of Origin	China	Outlet Type	GFCI, Self-Test, Tamper-Resistant
Application Sector	Commercial, Residential	Standard	RoHS, cULus
Warranty Type	1-Year from Day of Sale	Type	GFCI, Tamper-Resistant

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
------------------	---------	------------------	---------

Product Height US	4.2 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---	-----

Technical Information

Seismic Tested	No	Is Tamper-Resistant	Yes
Amperage	20 A	Is Weather Resistant	No
Indoor/Outdoor	Indoor	Wattage	2500 W