



Wiremold
25DTC-E10DG - 25DTC Series Blank Steel Tele-Power Express Pole (Designer Gray)
Part No. 25DTC-E10DG



Routing power, data, and A/V – neatly and simply – from up there to down here; that’s what Tele-Power® Poles are all about. Their sole purpose is to get the business end of your wire and cabling needs down to your workstation, equipment, or modular furniture. Specifically, in away-from-the-wall locations in open commercial office areas, schools, labs, stores and other sites. Whatever power, data, or A/V wiring you need to bring down to the desk, workstation, or cash registers, Wiremold Tele-Power Poles handle all of your needs effortlessly. For modular office furniture – our poles easily provide the hook up to feed office partitions. The poles are also available with specialized electrical circuits such as dedicated/isolated ground. Vertical drop poles give you the flexibility and capacity to devote both sides of the pole for single or dual service feeds. Legrand/Wiremold offers the broadest selection of open space solutions. With standard, custom and configurable products, you can rest assured that the right solution is readily available and adaptable to your current and future work environments.

Features & Benefits

Two sections of a two-compartment pole (5'4" (1.626m) base + 5' (1.524m) extender) assembles to form a 10' 4" (3.148m) pole. Nominal material thickness .040" (1.0mm). Ivory or gray boot base.

Relocatable. Ready for service in 30 minutes or less. Can be quickly reconfigured or relocated as work space uses and service needs change.

Dual-channel. Allows a single drop point for access to multiple services.

Wide selection of standard options. Stocked in a variety of materials, finishes, and heights.

Multiple color options. Available in four aesthetic colors: white, black, ivory, and gray.

Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless, aesthetically pleasing interface for voice, data, audio, and video applications at the point of use.

Pole extenders combine quick installation with easy job-site handling. Snap together 5' sections to create a pole or extend the length of your existing 25TP series pole.

Custom capabilities. Modify receptacle type and location, change color finish, alter pole heights, add fixture whips and more.

New extenders accommodate a variety of ceiling heights, can ship UPS or air freight for quick & reliable delivery.

Furnished unwired without outlets. Mounting hardware, entrance end plate and ceiling trim plate furnished. An 8" (203mm) cover at top front of pole is removable for making power wiring connections.

Specifications

General Info

Product Line	Wiremold	Color	Designer Gray
UPC Number	786776193435	Country Of Origin	United States
Product Series	Steel Tele-Power	Application Sector	Commercial

Standard	cULus Listed, Multioutlet Assemblies: File E15191, E178348		Type	Pole
Dimensions				
Product Width US	2.312 in		Product Weight US	21.3 lb
Product Height US	125.98 in			
Listing Agencies / 3rd Party Agencies				
cULus ListingNumber	E15191		cULus Listed	Yes
Trade Programs				
USMCA	Yes			
Additional Information				
RoHS Compliant	Yes			
Technical Information				
Cutout	2A, A/V, Data, Keystone		Number of Channels	2