Pass and Seymour

# 20A 125V Hospital-Grade Tamper-Resistant USB Type A/A Outlet, Gray

Part No. TR8300HUSBGRY

Designed for the healthcare market and capable of withstanding heavy use due to its UL Hospital Grade certification. Features include an improved overall 3.1A USB charging capability, auto-ground clips, zinc-plated ground terminal screw, as well as triple-wipe brass contacts for lasting retention. The screw-pressure-plate back wiring makes installation fast and easy. Also available in black, green, gray, ivory, light almond, nickel, red and white. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices

Multiple color options available.

Stainless steel auto-ground clips assure positive ground.

AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Gray |
| Finish | Matte | UPC Number | 785007031614 |
| Country Of Origin | China | Number of Receptacles | 2 |
| Features | USB-A Charging | Outlet Type | Tamper-Resistant, USB-Charging |
| Application Sector | Commercial, Hospital Grade | Type | Outlet |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 1.693 in | Product Depth US | 1.392 in |
| Product Height US | 2.677 in | | |

## Listing Agencies / 3rd Party Agencies

| | |
|---|---|
| cULus Listed | Yes |

## Additional Information

| | |
|---|---|
| Product Environmental Profile | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Is Tamper-Resistant | Yes | USB Amperage | 3.1 A |
| Number of USBs | 2 | USB Power Output | 15 W |
| Amperage | 20 A | Number of Poles | Double Pole |
| Indoor/Outdoor | Indoor | | |