NOTES
1. OPTICAL PERFORMANCE CHARACTERISTICS SHALL BE IN ACCORDANCE WITH SPECIFICATION 71800079C.
2. EXTERNAL PORTS OF THE ADAPTERS HAVE PROTECTIVE DUST CAPS INSTALLED.
3. ASSEMBLY IDENTIFICATION LABEL SHALL CONTAIN ASSY PART NUMBER, DATE CODE(WWYY=WEEK YEAR), LOCATION CODE(XX), SERIAL NUMBER, "BB", "CC/125", & "24F" (USE TABLE 1 FOR "BB & "CC").
4. THE "GGG" SUFFIX IN THE PART NUMBER DESIGNATES THE CORE SIZE OF FIBER.
5. LABEL SHOWING INSERTION LOSS VALUES, BY PORT, PROVIDED ASSEMBLED TO CASSETTE.
6. THE CASSETTE HOUSING IS BLACK ABS/PC. THE COVER IS CLEAR PC.
7. ALL DIMENSIONS ARE IN INCHES.
8. INTERNAL FIBER IS RIBBONIZED.

⬡ DENOTES NOTE REFERENCE.



PORT LAYOUT
(FRONT)



REAR LAYOUT
(REAR)



FIBER COLOR BY PORT, POLARITY "ZZ" = A1			
HARNESS 1		HARNESS 2	
PORT #	COLOR	PORT #	COLOR
1	BLUE	13	BLUE
2	ORANGE	14	ORANGE
3	GREEN	15	GREEN
4	BROWN	16	BROWN
5	SLATE	17	SLATE
6	WHITE	18	WHITE
7	RED	19	RED
8	BLACK	20	BLACK
9	YELLOW	21	YELLOW
10	VIOLET	22	VIOLET
11	ROSE	23	ROSE
12	AQUA	24	AQUA

FIBER TYPE			
"GGG"	TYPE	"X"	TIER
09	SM 9/125 (OS2)	1	1
09A	SM 9/125 (OS2)	1	1
50E	MM 50/125 (4.9 GHz-km)	1	1
		2	2
		3	3

"AA"	FRONT PNL ADAPTER
LA	LC (APC)
LC	LC (PC OR UPC)

TABLE 1 ③ ④ ⑤

"GGG"	"BB"	"CC"	LC COLOR
09	SM	9	BLUE
09A	SM	9	GREEN
50E	MM	50	AQUA



PART NUMBER LEGEND

*** NOTICE ***
THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) PROVIDED. NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF LEGRAND, INC. MANUFACTURING RELEASE, PRODUCT SPECIFICATIONS AND STANDARDS ARE SUBJECT TO CHANGE WITHOUT NOTICE.

	NAME	DATE
DWN	RJG	3/12/2018
CHK	DMS	3/12/2018
APPR	RH	3/19/2018

legrand® WWW.LEGRAND.US

TITLE
CASSETTE ASSY, M4, 24/F, LC QUAD, SPLICE

SIZE	CAD FILE	DWG NO	REV
B	M4AAQ24GGGRYZZC	M4AAQ24-GGGRYZZ	01

SCALE 1:2 SHEET 1 OF 1