



**Wiremold**  
**4AT Prewired Dual Service Evolution™ Poke-Thru Device-Black**  
Part No. 4ATCP2RBK



Designed for retrofit and new construction, Evolution Series 4" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. With 2 Gangs of capacity, you will be able to configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel, and multiple powder-coated finishes designed to match any space. Evolution Series 4" Poke-Thru devices are the perfect fit for kiosks, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture.

## Features & Benefits

**Prewired assembly:** Save on labor with a completely assembled, prewired poke-thru .

**Recessed devices:** All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.

**Unique cover design:** The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe.

**Surface style cover assemblies:** A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.

**2 hour fire rating:** Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.

**UL Listed and UL fire classified to U.S. and Canadian safety standards:** UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

**Controlled receptacles:** The only option on the market with two marked receptacles in a 4" poke-thru that also meets Title 24 Plug Load Control standards.

**Step-on-it installation:** Quick and easy installation without the need for additional fasteners or a second installer.

Evolution Series Poke-Thru Devices are available in multiple finishes, (BK) black, (GY) gray, (NK) nickel, (BS) brass, (BZ) bronze, (AL) aluminum, (AA) brushed aluminum, (SB) satin brass, and (SN) satin nickel to seamlessly match your environment.

**Open system for expanded compatibility:** Accepts industry standard power, communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.

Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.

## Specifications

### General Info

|              |              |                   |               |
|--------------|--------------|-------------------|---------------|
| Product Line | Wiremold     | Color             | Black         |
| UPC Number   | 786564090632 | Country Of Origin | United States |

|                                       |   |                               |  |
|---------------------------------------|---|-------------------------------|--|
| Features                              | Recessed  | Cover Style                   | Surface  |
| Number of Knockouts                   | 2   | Application Sector            | Commercial, Education, Healthcare, Hospitality       |
| Standard                              | UL Fire Classified, cULus, NEC                            | Warranty Type                 | 1-Year from Installation or 2-Years from Day of Sale |
| Type                                  | Poke-Thru   |                               |  |
| Dimensions                            |   |                               |  |
| Product Width US                      | 5.5 in  | Product Weight US             | 6.1 lb   |
| Product Volume US                     | 561.44 cu in  | Product Depth US              | 18.56 in   |
| Product Height US                     | 5.5 in  | Cubic Capacity                | 24.5 in³   |
| Core Hole Size                        | 4 in  | Knockout Size                 | 1-1/2 in, 3/4 in                                     |
| Listing Agencies / 3rd Party Agencies |   |                               |  |
| cULus ListingNumber                   | E2961   | cULus Listed                  | Yes  |
| Additional Information                |   |                               |  |
| RoHS Compliant                        | Yes   | Product Environmental Profile | Yes  |
| Technical Information                 |   |                               |  |
| Floor Type                            | Carpet, Concrete, Polished Concrete, Terrazzo, Tile, Wood | Is Pre-Wired                  | Yes  |
| Service Capacity                      | Dual  | Fire Rating                   | 2 hr   |
| Cable Entry                           | Conduit Stub, knockout                                    | Number of Outlets             | 2  |