



**Wiremold**  
**4AT Recessed Unwired Poke-Thru Stem Assembly**  
 Part No. 4STC



Designed for retrofit and new construction, Evolution Series 4" Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. 2-gangs of capacity allow you to configure services for the needs of your space. Evolution Series 4" Poke-Thru devices are the perfect fit for kiosks, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture.

## Features & Benefits

Designed for retrofit and new construction, Evolution Series 4" Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. 2-gangs of capacity allow you to configure services for the needs of your space. Evolution Series 4" Poke-Thru devices are the perfect fit for kiosks, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture.

**Unique Cover Design:** The cover opens a full 180 degrees with sliding doors to keep wires, connections and people safe.

**Open System for Expanded Compatibility:** Accepts industry standard power, communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.

**2 Hour Fire Rating:** Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.

**Recessed Devices:** All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.

**6 Finishes:** Evolution Series Poke-Thru Devices are available in six finishes to seamlessly match your environment.

**Plug Load Control up to 30 Feet:** Tested with Pass & Seymour® Wireless RF receptacles to control plug loads up to a distance of 30 feet when the cover is closed.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786564090915
Country Of Origin	United States	Construction	Assembled
Number of Knockouts	10	Application Sector	Commercial

Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. cULus Listed Nonmetallic Outlet Boxes and Fittings Classified for Fire Resistance: File R8209 Guide CEYY. Meets Article 300.21 300.22[C] and 314 of NEC.	Type	Poke-Thru
----------	---	------	-----------

### Dimensions

Product Width US	4.75 in	Product Height US	18.562 in
Cubic Capacity	24.5 cu in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

### Buy American Act Compliance

NAFTA	Yes
-------	-----

### Additional Information

RoHS Conformant	Yes
-----------------	-----

### Technical Information

Cable Entry	3/4 in trade size conduit for power, 1 1/2 in trade size conduit for data, .75 in	Number of Outlets	0
-------------	--	-------------------	---