



Wiremold
Evolution 6AT2PAV Series Recessed Prewired Audio/Video Assembly with Flush Style Cover
Part No. 6AT2PAVBZ



Designed for retrofit and new construction, Evolution Series 6" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. With 3 Gangs of capacity, you will be able to configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel, and multiple powder-coated finishes designed to match any space. Evolution Series 6" Poke-Thru devices are the perfect fit for kiosks, meeting rooms, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture. For carpet, tile, wood and laminate concrete floor coverings.

Features & Benefits

Prewired Assembly: Save on labor with a completely assembled, prewired poke-thru with every power receptacle already installed.

Step-on-it Installation. Quick and easy installation without the need for additional fasteners or a second installer.

Multiple Finishes: Evolution Series Poke-Thru Devices are available in multiple finishes: (BK) black, (GY) gray, (NK) nickel, (BS) brass, (BZ) bronze, (AA) brushed aluminum, (SB) satin brass and (SN) satin nickel to seamlessly match your environment.

A flush style cover for tile applications allows the Evolution Series Poke-Thru Devices to be adjusted to the same level as the top surface of the floor covering.

A flush style cover for tile applications allows the Evolution Series Poke-Thru Devices to be adjusted to the same level as the top surface of the floor covering.

Plug Load Control Up To 30 Feet: Tested with Pass & Seymour® Wireless RF receptacles to control plug loads up to a distance of 30 feet when the cover is closed.

Meets ADA Accessibility Guidelines. Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels.

UL Listed and UL Fire Classified to U.S. and Canadian safety standards. UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

Recessed Devices: All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.

Unique Cover Design: The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe.

Ideal for High Foot Traffic Environments: Satin brass, satin nickel and brushed aluminum finishes offer a more durable, high-end look with a tougher clear powder coat.

The flush cover is designed to be used for tile or wood floors and in higher traffic applications, where a low profile is a must.

A/V Ready: Plates included to accept industry standard communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.

3 hour fire rating: Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 3 hours, the longest of its type.

The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio

The flush cover is designed to be used for tile or wood floors and in higher traffic applications, where a low profile is a must.

Specifications

General Info

Product Line	Wiremold	Color	Bronze
UPC Number	786564089087	Country Of Origin	United States

Construction	Assembled	Features	Recessed
Cover Style	Flush	Application Sector	Commercial, Education, Healthcare, Hospitality
Standard	UL Fire Classified, cULus, NEC	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Poke-Thru		
Dimensions			
Product Weight US	9.32 lb	Cubic Capacity	24 in³
Core Hole Size	6 in	Knockout Size	3/4 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Floor Type	Carpet, Concrete, Tile, Wood	Is Pre-Wired	Yes
Service Capacity	Dual	Fire Rating	2 hr
Cable Entry	CONDUIT		