



## Legrand

6AT Prewired Evolution™ Poke Thru Device, Surface Style Cover, Bronze  
Part No. 6ATC2PBZ



Designed for retrofit and new construction, Evolution Series 6" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. With 3 Gangs of capacity, you will be able to configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel, and multiple powder-coated finishes designed to match any space. Evolution Series 6" Poke-Thru devices are the perfect fit for kiosks, meeting rooms, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture. For carpet, tile, wood and laminate concrete floor coverings.

### Features & Benefits

**Prewired assembly:** Save on labor with a completely assembled, prewired poke-thru with every power receptacle already installed.

**Recessed devices:** All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.

**"Step-on-it" installation:** Quick and easy installation without the need for additional fasteners or a second installer.

**Unique cover design:** The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe.

**Multiple finishes:** Evolution Series Poke-Thru Devices are available in multiple finishes, [BK] black, [GY] gray, [NK] nickel, [BS] brass, [BZ] bronze, [AL] aluminum, [AA] brushed aluminum, [SB] satin brass, [SN] satin nickel to seamlessly match your environment.

**Surface style cover assemblies:** A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.

**Open system for expanded compatibility:** Accepts industry standard power, communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.

**Plug load control up to 30 feet:** Tested with Pass & Seymour® Wireless RF receptacles to control plug loads up to a distance of 30 feet when the cover is closed.

**2 hour fire rating:** Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.

**Meets ADA accessibility guidelines:** Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.

**UL Listed and UL fire classified to U.S. and Canadian safety standards:** UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

### Specifications

#### General Info

Color Bronze

UPC Number 786564088813

Country Of Origin United States

Product Line Wiremold

Application Sector Commercial

Type Poke-Thru

Standard cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY. Meets Article 300.21, 300.22[C] & 314 of NEC.

Number of Knockouts 2

#### Dimensions

Product Volume US 854.14

---

Product Width US	7.25
------------------	------

---

Product Height US	7.25
-------------------	------

---

Product Weight US	9.44
-------------------	------

---

Product Depth US	16.25
------------------	-------

---

Core Hole Size	6 in
----------------	------

---

Cubic Capacity	24.5 cu in
----------------	------------

---

#### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

cULus ListingNumber	E2961
---------------------	-------

---

#### Buy American Act Compliance

---

NAFTA	Yes
-------	-----

---

#### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

Product Environmental Profile	Yes
-------------------------------	-----

---

#### Technical Information

---

Number of Outlets	4
-------------------	---

---