




Wiremold
861FFTC Series Furniture Feed Raised Floor Box Assembly
Part No. 861FFTCVY



Cover has two 1/2" trade size conduits and one 3/4" trade size threaded conduit opening for feeding cables and wires through the floor. Flush flanges available in a variety of colors/finishes. Slide covers match painted flange colors. Aluminum and brass covers shipped with black slide covers. Brass flange also available with nonmetallic brass-color slide holder. Die-cast aluminum construction with three 1/2" trade size knockouts: two on the sides and one on the bottom. 18 cu. in. (295 cu.cm) capacity. Requires a 4" (102mm) diameter hole.

Features & Benefits

Cover has two 1/2" trade size conduits and one 3/4" trade size threaded conduit opening for feeding cables and wires through the floor.

Flush flanges available in a variety of colors/finishes

Slide covers match painted flange colors

Aluminum and brass covers shipped with black slide covers

Brass flange also available with nonmetallic brass-color slide holder

Specifications

General Info

| | | | |
|---------------------|--|-------------------|---|
| Product Line | Wiremold | Finish | Brushed |
| UPC Number | 786564013839 | Country Of Origin | Mexico |
| Construction | Assembled | Cover Style | Flush, Furniture Feed |
| Number of Knockouts | 3 | Cover Material | Die-Cast Aluminum |
| Application Sector | Commercial | Standard | cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC. |
| Warranty Type | 1-Year from Installation or 2-Years from Day of Sale | Type | Floor Box |

Dimensions

| | | | |
|-------------------|--------|----------------|--------------------|
| Product Weight US | 2.5 lb | Cubic Capacity | 18 in ³ |
| Knockout Size | 1/2 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | E2961 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

Trade Programs

| | |
|-------|-----|
| USMCA | Yes |
|-------|-----|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|------------|--------------|------------------|--------|
| Floor Type | Raised, Wood | Service Capacity | Single |
|------------|--------------|------------------|--------|

| | | | |
|---------------------|------|--------------|--------|
| Minimum Floor Depth | 1 in | Box Capacity | 1 Gang |
|---------------------|------|--------------|--------|

| | |
|-------------|----------|
| Cable Entry | knockout |
|-------------|----------|