



Wiremold  
**881FC Ratchet-Pro Fire Classified Nonmetallic Round PVC Floor Box**  
Part No. 881FC



Round PVC Floor Box supplied with reusable concrete cap, conduit reducers, and conduit hub plugs. Available for single service only. Graduated cubic inch markings inside the box indicate volume capacity at any depth. Box has parallel conduit hubs eliminating the need for 90 degree sweeps in installation. One-piece reduction from 1" to 1/2" (25mm to 12.7mm) conduit. Reducers and plugs located on a mounting bar for easier selection. For concrete pours of 2 1/4" to 6" (57mm to 152mm). Includes one 881ADP Adapter Ring. Box preserves the 2-hour fire rating of the floor in which it has been installed.

## Features & Benefits

Round PVC Floor Box supplied with reusable concrete cap, conduit reducers, and conduit hub plugs. Available for single service only.

One-piece reduction from 1" to 1/2" (25mm to 12.7mm) conduit. Reducers and plugs located on a mounting bar for easier selection. For concrete pours of 2 1/4" to 6" (57mm to 152mm).

Graduated cubic inch markings inside the box indicate volume capacity at any depth. Box has parallel conduit hubs eliminating the need for 90 degree sweeps in installation.

Includes one 881ADP Adapter Ring. Box preserves the 2-hour fire rating of the floor in which it has been installed.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786564072126
Country Of Origin	United States	Construction	Assembled
Number of Knockouts	2	Application Sector	Commercial, Education, Healthcare, Hospitality
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

### Dimensions

Product Weight US	4.3 lb	Cubic Capacity	56 in <sup>3</sup>
Knockout Size	1 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E110748	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Concrete	Service Capacity	Single
------------	----------	------------------	--------

Fire Rating	2 hr	Box Capacity	1 Gang
-------------	------	--------------	--------

Cable Entry	CONDUIT	Box Type	Fire Classified
-------------	---------	----------	-----------------

Depth Behind Device Plates	1.75 in
----------------------------	---------