



adorne Collection  
adorne® 65W USB Outlet, Plus-Size, Type C, 15A, Tamper-Resistant, Graphite  
Part No. ARTRUSB15PD65G4



Features dual Type-C charging ports with 65W each, providing the fastest USB charging for phones, tablets and laptops. Includes two 15-amp AC receptacles. Advanced Power Delivery provides intelligent charging that negotiates optimal voltage and current between the outlet and the device being charged. Easily replaces a traditional outlet in as little as ten minutes. Enjoy USB charging functionality in every room of your home with the unique adorne contemporary aesthetic. Made exclusively for use with plus-size, screwless wall plates from the adorne® Collection, sold separately.

## Features & Benefits

Charges the latest electronics, including small laptops like the 13-in MacBook Pro, Chromebooks, and Microsoft Surface Pro 9 thanks to industry-leading amperage and 65W of power courtesy of advanced Power Delivery

Power Delivery feature provides intelligent charging that negotiates optimal voltage and current between the outlet and the device being charged to ensure fastest charging speeds.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect

UL tested to ensure protection against electrical shock, fire and other hazards.

Dual USB-C ports eliminate the need to upgrade devices for the foreseeable future and maximize available outlets as no bulky charging bricks are required.

For complete installation, device must be paired with an adorne® PLUS-SIZE screwless wall plate (not included). Available in a range of contemporary colors and stunning finishes.

Fast, easy installation: fits in a standard electrical box; no custom-cut electrical boxes needed. Standard wire leads expedite installation.

Intelligent thermal sensing feature prevents overheating of either the device or charger.

Integrated GaN technology delivers faster, more efficient charging with less heat generation and 22% lower energy use per watt delivered, compared to previous technology.

Proprietary indicator light displays charging status at a glance (light glows yellow while charging is in progress and green when the battery is sufficiently charged).

Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Limited Lifetime Warranty.

## Specifications

### General Info

|              |                |                   |          |
|--------------|----------------|-------------------|----------|
| Product Line | Pass & Seymour | Color             | Graphite |
| UPC Number   | 785007461107   | Country Of Origin | China    |

|                                       |                                |                      |                                  |
|---------------------------------------|--------------------------------|----------------------|----------------------------------|
| Number of Receptacles                 | 2                              | Features             | Indicator Lights, USB-C Charging |
| Outlet Type                           | Tamper-Resistant, USB-Charging | Application Sector   | Multi-Dwelling Unit, Residential |
| Wall Plate Included                   | No                             | Standard             | cULus                            |
| Warranty Type                         | Limited Lifetime Warranty      |                      |                                  |
| Dimensions                            |                                |                      |                                  |
| Product Width US                      | 1.67 in                        | Product Weight US    | 0.54 lb                          |
| Product Depth US                      | 1.62 in                        | Product Height US    | 1.94 in                          |
| Product Length US                     | 4.2 in                         |                      |                                  |
| Listing Agencies / 3rd Party Agencies |                                |                      |                                  |
| cULus Listed                          | Yes                            | cUL Listed           | Yes                              |
| Additional Information                |                                |                      |                                  |
| Energy Savings                        | No                             |                      |                                  |
| Technical Information                 |                                |                      |                                  |
| Connection Location                   | Back Only                      | USB Wattage          | 65 W                             |
| Number of Wires                       | 3                              | Amperage             | 15 A                             |
| Indoor/Outdoor                        | Indoor                         | Wire Connection Type | Flying Leads                     |
| Voltage                               | 125.0 V                        |                      |                                  |