



Use this wired smart light switch to control the Wake/Sleep lighting scenes with one touch. Position near a nightstand or the door of an en suite bathroom for convenient morning and nighttime control. Easily replace an existing switch, then program it easily within the app. The switch requires a Smart Gateway with Netatmo to be installed and must be paired with the gateway. Once paired with the gateway, you can add other Smart Lighting with Netatmo devices to your Wake/Sleep scenes that the switch is programmed to run. Made exclusively for use with Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Smart Gateway with Netatmo REQUIRED

One-Touch Control: Enjoy simple control of four lighting scenes (not including Home/Away and Wake/Sleep). Easily create and manage scenes from your smartphone or tablet using the Legrand Home + Control app

Easy Installation: Installs in a standard electrical box with push-in connections and wire leads (neutral wire required).

Reliable Performance: Features ultra-reliable performance through a robust and dedicated mesh network

Part of the adorne with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets.

Compatible with Smart Home Platforms: Can be onboarded to Amazon Alexa, Google Home and Apple Home, as well as other smart home platforms for greater home integration.

Multiple Collections & Color Options: Choose from either the adorne® or radiant® collection to fit a home's unique needs. Additional color options available with use of Smart Lighting with Netatmo Color Change Kits

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Gloss	UPC Number	785007446562
Country Of Origin	China	Material	Polycarbonate
Features	Smart Lighting, With Netatmo	Switch Type	sofTap
Number of Switches	1	Works With	Amazon Alexa, Apple Home Kit, Google Home

Application Sector	Commercial, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Standard	UL, cULus, FCC, ICC	Warranty Type	2-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.77 in	Product Weight US	0.122 lb
Product Depth US	1.17 in	Product Height US	1.45 in
Product Length US	2.66 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Additional Information

RoHS Compliant	Yes		
----------------	-----	--	--

Technical Information

Connection Location	Back Only	Terminal Accommodation	#14 AWG - #12 AWG
Connection	Wired	Number of Gangs	1
Amperage	0.1 A	Number of Poles	Multi-Location
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Mounting Type	In-Wall	Location Rating	Dry
Wire Connection Type	Internal Terminal Screw	Voltage	120 VAC
