Wiremold

**AMDTP-412 - AMDTP-4 Series Aluminum Tele-Power Pole**

Part No. AMDTP-412



Two-compartment pole (power and communications). Nominal material thickness .050'' (1.8mm). Length: 12' 5''(3.8m. Factory wired with 20A 125V fed-spec general grade duplex style receptacles. An opening for communication and a 1/2'' (12.7mm) hole for power is provided at top. The 8'' (203mm) cover at top front of pole is removable for making power wiring connections. Communication KOs provided for RJ11/RJ45 and modular furniture connectors. Mounting hardware, entrance end fitting, and ceiling trim plates furnished. Anodized aluminum finish. Available in standard length of 10' 5'' (3.2m), 12' 5''(3.8m), and 15' 5'' (4.7m). NOTE 1: Custom colors, other lengths (20' (6.1m) max.) or additional circuits are available on custom orders. Consult factory for more information. Can be factory- or field-wired with many commercially available devices. NOTE 2: Add the suffix ''-C'' for the cord-ended version (10' (3.0m) cord). Cord-ended version AVAILABLE IN CANADA ONLY.

## Features & Benefits

Two-compartment pole (power and communications). Nominal material thickness .050'' (1.8mm). Length: 12' 5''(3.8m. Factory wired with 20A 125V fed-spec general grade duplex style receptacles. An opening for communication and a 1/2'' (12.7mm) hole for power is provided at top. The 8'' (203mm) cover at top front of pole is removable for making power wiring connections. Communication KOs provided for RJ11/RJ45 and modular furniture connectors. Mounting hardware, entrance end fitting, and ceiling trim plates furnished. Anodized aluminum finish. Available in standard length of 10' 5'' (3.2m), 12' 5''(3.8m), and 15' 5'' (4.7m). NOTE 1: Custom colors, other lengths (20' (6.1m) max.) or additional circuits are available on custom orders. Consult factory for more information. Can be factory- or field-wired with many commercially available devices. NOTE 2: Add the suffix ''-C'' for the cord-ended version (10' (3.0m) cord). Cord-ended version AVAILABLE IN CANADA ONLY.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Wiremold | UPC Number | 786776088397 |
| Country Of Origin | United States | Standard | cULus Listed Multioutlet Assemblies: File E15191 E178348 Guide PVGT, Raceway Fittings: File E41751 Guide RJPR, Accessories: File E53857 Guide RVUR Meets Article 380 & 386 of NEC |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 2.312 in | Product Height US | 149.86 in |

## Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| cULus ListingNumber | E15191 | cULus Listed | Yes |

## Buy American Act Compliance

| | |
|---|---|
| NAFTA | Yes |

## Additional Information

| | | | |
|---|---|---|---|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |