



Charge phones, tablets and more up to 40% faster, with USB Outlets from the adorne® Collection. This solution adds advanced Power Delivery to provide fast in-wall charging without an adapter. Easily replacing traditional outlets in as little as ten minutes, this USB Outlet transforms your space with modern functionality and the unique, contemporary aesthetic of adorne. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate(not included). Available in a range of contemporary colors and stunning finishes.

Built for intelligent charging, the outlet detects and delivers the precise amount of power needed to maximize charging speeds.

Helpful indicator light lets you see charging status at a glance. Light glows yellow while charging is in progress, and shows green once the device battery is sufficiently charged.

Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

Charges the latest devices up to 2X faster with 6.0 amps and 30W of power courtesy of advanced Power Delivery.

Provides fast and convenient built-in charging through two future-proof USB Type-C ports, accommodating new and upcoming devices without an adapter.

Includes multiple layers of overcurrent protection, ensuring the outlet and your favorite devices can charge at optimal levels without risk of damage.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Graphite
UPC Number	785007378092	Country Of Origin	China
Number of Receptacles	2	Features	USB-C Charging
Outlet Type	Tamper-Resistant, USB-Charging	Application Sector	Commercial, Multi-Dwelling Unit, Residential

---

Wall Plate Included	No	Warranty Type	Limited Lifetime Warranty
---------------------	----	---------------	---------------------------

---

## Dimensions

---

Product Width US	2.5 in	Product Depth US	1.77 in
------------------	--------	------------------	---------

---

Product Height US	3.0 in
-------------------	--------

---

## Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

## Technical Information

---

Is Tamper-Resistant	Yes	Connection Location	Back Only
---------------------	-----	---------------------	-----------

---

USB Wattage	30 W	USB Amperage	6 A
-------------	------	--------------	-----

---

Connection	USB Type C/C	Number of USBs	2
------------	--------------	----------------	---

---

Number of Wires	3	Output Current	6A
-----------------	---	----------------	----

---

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

---

Number of Poles	Double Pole	Wire Size	14 - 12 AWG
-----------------	-------------	-----------	-------------

---

Indoor/Outdoor	Indoor	Mounting Type	Box
----------------	--------	---------------	-----

---

Wire Connection Type	Internal Pressure Plates	Voltage	125.0 V
----------------------	--------------------------	---------	---------

---

Environmental Conditions	95% (relative humidity, non-condensing)
--------------------------	---

---