



**Wiremold**  
**Evolution Series EFB45 Floor Box Surface Style Cover with Carpet Insert**  
Part No. EFB45CTCBK



Evolution™ Series black powder coated Surface-style cover with floor covering insert lid is a low profile cover designed to attach to the EFB45S style floor boxes. Each cover is made of die cast aluminium and is equipped with a durable hinge allowing the cover to rotate open 180 degrees, and two (2) slide egress doors that lock in the open position and automatically close around the cables when the cover is closed. The flange has a beveled edge that meets ADA guidelines and reduces tripping hazards. These cover assemblies are designed to sit on top of finished floor such as: carpet, tile, wood, polished concrete, and terrazzo. Also available in six (6) powder coat finishes: black (BK), gray (GY), brass (BS), nickel (NK), aluminium (AL) and bronze (BZ).

## Features & Benefits

Die cast aluminum cover assemblies. Floor Box Covers have been designed to work on multiple floor surfaces and are manufactured from die cast aluminum to provide strength and style. Decorative powder coat colors (black gray) and durable finishes (brushed aluminum, satin brass, satin nickel) will complement any room décor.

Auto-close egress doors. Cable egress doors lock in position when open and automatically closes around wires to protect cabling and reduce trip hazards.

Hinge design enables covers to open a full 180° and lie flat on the floor surface with the durability to support a large cover. Provides easy access to all interior modules and activations while reducing tripping hazards.

## Specifications

### General Info

Product Line	Wiremold	Color	Black
Finish	Powder Coat	UPC Number	786564086307
Country Of Origin	India	Construction	Assembled
Application Sector	Commercial	Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.
Type	Floor Box		

### Dimensions

---

Product Width US	9.938 in	Product Weight US	6.9 lb
------------------	----------	-------------------	--------

---

Product Volume US	169.81 cu in	Product Depth US	13.75 in
-------------------	--------------	------------------	----------

---

Product Height US	1.188 in	Product Length US	13.875 in
-------------------	----------	-------------------	-----------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

---

### Additional Information

---

RoHS Conformant	Yes	Product Has Potential to Contribute to LEED	Yes
-----------------	-----	---	-----

---

Product Environmental Profile	Yes
-------------------------------	-----

---

### Technical Information

---

Number of Outlets	0
-------------------	---

---