



Wattstopper
Discontinued - DLM Wireless Pre-Eng Wall Switch, ON/OFF w/Arrows, All, Teaching, General, AV, White
Part No. LMSW-605-W-ENG4



The LMSW-605 Scene Switch is a wireless device that can set and recall preset lighting scenes and raise and lower lighting levels. It is part of the NEW wireless Digital Lighting Management (DLM) system and controls loads connected to DLM room controllers by recalling any four of the 16 scenes available in a DLM local network. It can function as a part of a completely wireless room pairing with a wireless room controller (LMRC-611MCC) or used in a hybrid wired & wireless room to control loads connected to a traditional wired room controllers when used in conjunction with a wireless bridge (LMBC-650).

Features & Benefits

Wireless Digital 5-Button Scene Switch

It is part of the NEW wireless Digital Lighting Management (DLM) system and controls loads connected to DLM room controllers by recalling any four of the 16 scenes available in a DLM local network

Built-in IPv6 Mesh and Bluetooth antennas provide robust signal strength and reliable communication

Paddle with LED status indicator allows raise/lower control of scenes or loads

Ground wire allows you to install next to a line voltage device. This wire is only needed when placed next to a line voltage device in the same box. Grounding cables are otherwise not needed if in a purely low voltage application.

The LMSW-605 Scene Switch is a wireless device that can set and recall preset lighting scenes and raise and lower lighting levels

It can function as a part of a wireless room with a wireless room controller (LMRC-611MCC) or used in a hybrid wired/wireless room to control loads connected to a traditional wired room controllers when used with a wireless bridge (LMBC-650).

Uses IPv6 Mesh to establish network communication with all DLM wireless devices

Quick and easy wireless installation – no Cat 5e connection needed

Low voltage switches for control of four customizable scenes

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182945603
Country Of Origin	China	Product Series	LMSW
Switch Type	Push	Number of Switches	5
Application Sector	Commercial	Standard	UL, cUL, FCC part 15, RoHS
Warranty Type	5-Year	Type	Switch

Dimensions

Product Width US	1.8 in	Product Weight US	0.2 lb
Product Volume US	19.845 cu in	Product Depth US	1.6 in

Product Height US	4.2 in		
Technical Information			
Operating Temperature Min	0 °C	Compatibility	DLM Wireless (IPv6), LMBC-650
Has Battery	Yes	Number of Connections	0
Battery Capacity	1500 mAh	Frequency Band	2.4 GHz
Operating Temperature Max	40 °C	Number of Buttons	5
Number of Rockers	0	Wireless Range	Bluetooth, up to 30 ft, IPv6 6LoWPAN, up to 60 ft
Topology	Wireless Mesh	Antenna	Integrated, Internal
Input Voltage	3 VDC	Indoor/Outdoor	Indoor
Battery Life	Up to 10 Years	Mounting Type	J-Box
Battery	CR123A 3V	Operating Temperature	0°-40°C, 32°-104°F
Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	Wireless
Antenna Pattern	Omni-directional	Engraving Type	Text
Encryption	AES 128-bit	Storage Temperature	23° - 140° F, -5° - 60° C