



4' Plugmold Plus Multioutlet Strip comprised of four 12 inch parts, GB 15 Amp

## Features & Benefits

Nonmetallic, lightweight with snap-on cover. Speeds installation: provides easy access to wiring for changes or additions.

Full range of fittings. Facilitates easy installation of wiring for whatever the job: communication workstation outlets, receptacles, switches and more. Over lapping fittings permit neat butting to raceway.

NEMA heavy duty duplex receptacles independently tested to Fed. Spec. WC596G performance criteria. Enhanced product quality ensures dependable performance.

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

Customization available. All products can be modified to accommodate virtually any application.

Tapered profile design with textured ivory finish. Blends with surroundings in office, display space, dorm rooms and residential locations.

Factory wired harness available with duplex receptacles on multiple spacings. Maximum power distribution to the point of use.

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates the need for multiple splicing, speeding up installations on long runs.

Field replaceable surge module. No need to remove the raceway cover to splice in a replacement receptacle. Field changes and maintenance are quick and easy.

## Specifications

### General Info

|                   |               |                       |              |
|-------------------|---------------|-----------------------|--------------|
| Product Line      | Wiremold      | UPC Number            | 786776519983 |
| Country Of Origin | United States | Number of Receptacles | 4            |

|                                       |            |                          |   |
|---------------------------------------|------------|--------------------------|---|
| Application Sector                    | Commercial | Standard                 | cULus Listed Base & Blank Cover: File E90378 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E90377 GuideRJPR. Base & Blank Cover & Plugmold Series w/Snapcoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC. |
| Type                                  | Plugmold   |                          |   |
| Dimensions                            |            |                          |   |
| Product Width US                      | 1.75 in    | Product Weight US        | 2.08 lb   |
| Product Depth US                      | 1.0 in     | Product Length US        | 1.75 in   |
| Listing Agencies / 3rd Party Agencies |            |                          |   |
| cULus ListingNumber                   | E15191     | cULus Listed             | Yes   |
| Trade Programs                        |            |                          |   |
| USMCA                                 | Yes        |                          |   |
| Additional Information                |            |                          |   |
| RoHS Compliant                        | Yes        |                          |   |
| Technical Information                 |            |                          |   |
| Amperage                              | 15 A       | Enclosure Type           | Non-Metallic  |
| Voltage                               | 120.0 V    | Environmental Conditions | Dry interior locations  |