



Ortronics
Mighty Mo 20 PDU Mounting Brackets, Rack Mount, 1 Deep, 1 Wide, Black
Part No. MM20PDUMB1D1W-B



Legrand Mighty Mo 20 PDU Mounting Bracket Kits are designed to mount “Button Mount” PDUs to the VMD style vertical managers or rear channels of the Mighty Mo 20 open racks. Offset, Flat and Vertical manager style brackets are available, which provide multiple mounting options.

Features & Benefits

Multiple Mounting Options: Mount offset to the rack rails on the left or right-side of the rack, at multiple heights to accommodate a button mount PDU.

Direction Mounting: Offset mounts enable parallel or perpendicular mounting.

Color Matched: Available in Black or White to match the Mighty Mo 20 rack.

Cable Management: Brackets accept ¼ turn accessories and are compatible with cable spools, and 3-inch or 6-inch cable rings to manage a PDU.

Single Deep, Single Wide PDU Brackets: Mount 1 PDUs offset, parallel to the rack, or 1 PDU perpendicular to the rack.

Specifications

General Info

| | | | |
|-------------------|-----------------------|--------------------|-------------------------|
| Product Line | Ortronics | Color | Black |
| Finish | Powder Coat | UPC Number | 662875343707 |
| Country Of Origin | United States | Material | Steel |
| Included | Hardware for mounting | Application Sector | Commercial, Data Center |
| Standard | RoHS | Warranty Type | 5-Year |
| Type | Bracket | | |

Dimensions

| | | | |
|------------------|---------|-------------------|--------|
| Product Width US | 4.21 in | Product Weight US | 0.7 lb |
|------------------|---------|-------------------|--------|

| | | | |
|------------------|---------|-------------------|---------|
| Product Depth US | 2.36 in | Product Height US | 5.75 in |
|------------------|---------|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|--------------|-----|-----------------|-----|
| CE Certified | Yes | REACH Compliant | Yes |
|--------------|-----|-----------------|-----|

Additional Information

| | | | |
|----------------|-----|----------------|----|
| RoHS Compliant | Yes | Energy Savings | No |
|----------------|-----|----------------|----|

Technical Information

| | | | |
|---------------|-----------|--------------------|--------|
| Compatibility | Mighty Mo | Mounting Hole Type | Tapped |
|---------------|-----------|--------------------|--------|

| | | | |
|-----------------------|-------|-------|----------------------------|
| Mounting Rail Spacing | 19 in | Frame | Adjustable, Channel, Fixed |
|-----------------------|-------|-------|----------------------------|

| | |
|----------|------------|
| Mounting | Rack Mount |
|----------|------------|
