



radiant Collection
radiant® 30W USB Outlet, Type C, 15A, Tamper-Resistant, Brown
Part No. R26USBPDC6



Made to deliver a 30 Watts of power and featuring two built-in Type-C USB connections, this solution adds advanced Power Delivery to the industry-leading amperage of our USB line. The result is a faster, future-proof option for convenient in-wall charging, specially designed to optimize performance for your Power Delivery-enabled devices. Easily replace a traditional outlet in as little as ten minutes to gain the modern functionality of intelligent charging for maximized speeds, complete with multi-layered overcurrent protection to keep the outlet and your devices safe from damage. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

| | |
|--|---|
| Charges the latest devices up to 2X faster with 6.0 amps and 30W of power courtesy of advanced Power Delivery. | Built for intelligent charging, the outlet detects and delivers the precise amount of power needed to maximize charging speeds |
| Provides fast and convenient built-in charging through two future-proof USB Type-C ports, accommodating new and upcoming devices without an adapter | Helpful indicator light lets you see charging status at a glance. Light glows yellow while charging is in progress, and shows green once the device battery is sufficiently charged |
| Includes multiple layers of overcurrent protection, ensuring the outlet and your favorite devices can charge at optimal levels without risk of damage | All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty |
| Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect | Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation |
| More color options available to fit any style, including finishes to match current hardware and lighting trends | |

Specifications

General Info

| | | | |
|-------------------|-----------------------|--------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Brown |
| Finish | Matte | UPC Number | 785007290066 |
| Country Of Origin | China | Features | USB-C Charging |
| Outlet Type | USB-Charging | Application Sector | Commercial, Residential |
| Type | Tamper-Resistant, USB | | |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.693 in | Product Depth US | 1.35 in |
| Product Height US | 4.18 in | | |

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|----------------|--------|------------------|--------------|
| USB Amperage | 6 A | Connection | USB Type C/C |
| Output Current | 6A | USB Power Output | 30 W |
| Amperage | 15 A | Current Rating | 15 A |
| Indoor/Outdoor | Indoor | Mounting Type | Box |