



The Wired Smart Home/Away Switch allows you to hardwire a 2-button switch dedicated to controlling your Home/Away scenes configured in the Legrand Home + Control App. The switch requires a Smart Gateway with Netatmo to be installed and must be paired with the gateway. Once paired with the gateway, you can add other Smart Lighting with Netatmo devices to your Home/Away scenes that it is programmed to run. A great solution for providing easy access to turn lights on and off when you arrive or depart your home. Made exclusively for use with Wall Plates from the radiant® Collection.

## Features & Benefits

### Smart Gateway with Netatmo REQUIRED

**One-Touch Control:** Enjoy simple one-touch control of Home/Away scenes. Manage scenes using your smartphone or tablet using the Legrand Home + Control app.

**Easy Installation:** Installs in a standard electrical box with push-in connections and wire leads (neutral wire required).

**Reliable Performance:** Features ultra-reliable performance through a robust and dedicated mesh network

Part of the radiant with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets.

**Compatible with Smart Home Platforms:** Can be onboarded to Amazon Alexa, Google Home and Apple Home, as well as other smart home platforms for greater home integration.

**Multiple Collections & Color Options:** Choose from either the adorne® or radiant® collection to fit a home's unique needs. Additional color options available with use of Smart Lighting with Netatmo Color Change Kits

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007446838
Country Of Origin	China	Features	Smart Lighting, With Netatmo
Switch Type	Paddle	Number of Switches	1

Works With	Amazon Alexa, Apple Home Kit, Google Home	Device Front Face Size	Full-Size
Device Backbody Size	Full-Size	Application Sector	Commercial, Residential
Wall Plate Included	Yes	Standard	UL, cULus, FCC, ICC
Warranty Type	1-Year	Type	Switch

### Dimensions

Product Width US	1.81 in	Product Weight US	0.159 lb
Product Depth US	1.11 in	Product Height US	1.5 in
Product Length US	4.78 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

Connection Location	Back Only	Terminal Accommodation	#14 AWG - #12 AWG
Number of Gangs	1	Amperage	0.1 A
Number of Poles	Multi-Location	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	In-Wall
Wire Connection Type	Screw Terminal	Voltage	120 VAC