



**Wiremold**  
**RC3 Multi-Service Poke-Thru Assembly, Black**  
Part No. RC3ATCBK



Assembled unit. Prewired 20A duplex receptacle can be wired as a standard duplex receptacle or isolated ground. Flange available in painted gray (GY), black (BK), ivory (VY) or brushed metal finishes in aluminum (AL), and brass (BS). Slide covers match the painted flange colors: gray, black, and ivory. Aluminum and brass flanges shipped with black slide cover. Brass flange also available with nonmetallic brass colored slide holder (AB). Aluminum flange also available with nonmetallic aluminum colored slide holder (AA). Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers. Unit also includes two Ortronics TracJack adapters and two Ortronics Series II adapters. Modular jacks sold separately. NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC3 Series Poke-Thru Devices require a 4inch (102mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8inch minimum.

## Features & Benefits

|   |  |
|---|--|
| Assembled unit Prewired 20A duplex receptacle can be wired as a standard duplex receptacle or isolated ground       | Flange available in painted gray (GY), black (BK), ivory (VY) or brushed metal finishes in aluminum (AL), and brass (BS) |
| Slide covers match the painted flange colors: gray, black, and ivory  | Aluminum and brass flanges shipped with black slide cover  |
| Brass flange also available with nonmetallic brass colored slide holder (AB)  | Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers      |
| Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers | Unit also includes two Ortronics TracJack adapters and two Ortronics Series II adapters                                  |
| Modular jacks sold separately   | NOTE: Assembled with scrub water gasket  |
| For use on tile or carpet floors  | Modular jacks sold separately  |
| Not designed to work with bare concrete or terrazzo   | Floor covering thickness 1/8" minimum  |

## Specifications

### General Info

|                     |              |                    |  |
|---------------------|--------------|--------------------|--|
| Product Line        | Wiremold     | Color              | Black  |
| UPC Number          | 786564067047 | Country Of Origin  | Mexico   |
| Number of Knockouts | 2            | Application Sector | Commercial, Education, Healthcare, Hospitality |

|                                       |                                |                               |  |
|---------------------------------------|--------------------------------|-------------------------------|--|
| Standard                              | UL Fire Classified, cULus, NEC | Warranty Type                 | 1-Year from Installation or 2-Years from Day of Sale |
| Type                                  | Poke-Thru                      |                               |  |
| Dimensions                            |                                |                               |  |
| Product Width US                      | 7.5 in                         | Product Weight US             | 5.247 lb   |
| Product Volume US                     | 900.0 cu in                    | Product Depth US              | 16.0 in  |
| Product Height US                     | 7.5 in                         | Cubic Capacity                | 24.5 in <sup>3</sup>                                 |
| Core Hole Size                        | 4 in                           |                               |  |
| Listing Agencies / 3rd Party Agencies |                                |                               |  |
| cULus ListingNumber                   | E2961                          | cULus Listed                  | Yes  |
| Additional Information                |                                |                               |  |
| RoHS Compliant                        | Yes                            | Product Environmental Profile | Yes  |
| Technical Information                 |                                |                               |  |
| Floor Type                            | Carpet, Tile                   | Is Pre-Wired                  | Yes  |
| Service Capacity                      | Dual                           | Fire Rating                   | 2 hr   |
| Number of Outlets                     | 2                              |                               |  |