



Wiremold
RC4 Multi-Service Poke-Thru Assembly, Black
Part No. RC4ATCBK



Unit includes four prewired 20A receptacles. Each duplex receptacle is wired as separate circuit. The duplex can be wired as a standard receptacle or isolated ground. Finish flange available in gray (GY), black (BK), ivory (VY) or brushed metal finishes in aluminum (AL), and brass (BS). Aluminum and brass flanges shipped with black slide cover. Brass flange also available with nonmetallic brass colored slide holder (AB). Aluminum flange also available with nonmetallic aluminum colored slide holder (AA). Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers. Unit also includes Ortronics TracJack Mounting adapters and Ortronics Series II Communication Housing. Modular jacks sold separately. NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC4 Series Poke-Thru Devices require a 4inch (102mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8inch minimum.

Features & Benefits

Unit includes four prewired 20A receptacles. Each duplex receptacle is wired as separate circuit.

Aluminum and brass flanges shipped with black slide cover. Brass flange also available with nonmetallic brass colored slide holder (AB). Aluminum flange also available with nonmetallic aluminum colored slide holder (AA).

NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC4 Series Poke-Thru Devices require a 4inch (102mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8inch minimum.

The duplex can be wired as a standard receptacle or isolated ground. Finish flange available in gray (GY), black (BK), ivory (VY) or brushed metal finishes in aluminum (AL), and brass (BS).

Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers. Unit also includes Ortronics TracJack Mounting adapters and Ortronics Series II Communication Housing. Modular jacks sold separately.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786564131540	Country Of Origin	Mexico
Number of Knockouts	2	Application Sector	Commercial, Education, Healthcare, Hospitality
Standard	UL Fire Classified, cULus, NEC	Warranty Type	1-Year from Installation or 2-Years from Day of Sale

Type	Poke-Thru		
Dimensions			
Product Width US	8.25 in	Product Weight US	5.347 lb
Product Volume US	1114.86 cu in	Product Depth US	16.38 in
Product Height US	8.25 in	Cubic Capacity	24.5 in³
Core Hole Size	4 in	Knockout Size	3/4 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Floor Type	Carpet, Tile, Wood	Is Pre-Wired	Yes
Service Capacity	Dual	Fire Rating	2 hr
Number of Outlets	4		