



All communication device accepts up to four UTP connectors. Flange available in painted gray (GY), black (BK), ivory (VY), and brushed metal finishes in aluminum (AL) and brass (BS). Aluminum and brass flanges shipped with black cover. Brass flange also available with brass colored cover assembly (AB). Aluminum flange also available with aluminum colored cover assembly (AA). Unit includes two (2) Ortronics TracJack adapters, two (2) Ortronics Series II adapters, and two (2) Wiremold Open System adapters. Modular jacks sold separately. NOTE: Includes two Cat 6 TechChoice discrete keystone connectors, two Ortronics TracJack adapters, and two Wiremold Open System adapters. RC9AMD Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

## Features & Benefits

All communication device accepts up to eight UTP, fiber optic, audio, or video connectors	Finish flange available in gray (GY), black (BK), ivory (VY), brushed aluminum (AL) and brass finish (BS)
Aluminum and brass flanges standard with black cover	Aluminum flange also available with an aluminum colored nonmetallic cover (AA)
Brass flange also available with brass colored nonmetallic cover (AB)	Includes adapters to accept eight (8) Ortronics TracJack modular jacks, four (4) Ortronics Series II modular jacks, or Wiremold Open System adapters
Modular jacks sold separately.	NOTE: Assembled with scrub water gasket
For use on tile or carpet floors	AMD8 Series Poke-Thru Devices require a 4" (102mm) diameter hole
Not designed to work with bare concrete or terrazzo	Floor covering thickness 1/8" minimum

## Specifications

### General Info

Product Line	Wiremold	Color	Gray
UPC Number	786564006534	Country Of Origin	Mexico
Construction	Assembled	Cover Style	Surface
Number of Knockouts	1	Application Sector	Commercial, Education, Healthcare, Hospitality
Standard	UL Fire Classified, cULus, NEC	Warranty Type	1-Year from Installation or 2-Years from Day of Sale

Type	Poke-Thru
------	-----------

Dimensions

Product Weight US	2.981 lb	Core Hole Size	3 in
-------------------	----------	----------------	------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Carpet, Tile	Service Capacity	Dual
Fire Rating	2 hr	Cable Entry	CONDUIT