



The Wired Smart Scene Controller allows you to hardwire a 4-button switch dedicated to controlling various scenes as configured in the Legrand Home + Control App. The scene controller requires a Smart Gateway with Netatmo to be installed and must be paired with the gateway. Once paired with the gateway, you can add other Smart Lighting with Netatmo devices to up to 4 different scenes that the controller is programmed to run. A great addition for setting the proper mood in living rooms, dens, bedrooms, and more. Made exclusively for use with Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

- Smart Gateway with Netatmo REQUIRED** One-Touch Control: Enjoy simple control of four lighting scenes (not including Home/Away and Wake/Sleep). Easily create and manage scenes from your smartphone or tablet using the Legrand Home + Control app
- Easy Installation:** Installs in a standard electrical box with push-in connections and wire leads (neutral wire required). Part of the radiant with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets.
- Must be used in conjunction with installed Smart Switches, Dimmers and/or Outlets with Netatmo for scenes.** Compatible with Smart Home Platforms: Can be onboarded to Amazon Alexa, Google Home and Apple Home, as well as other smart home platforms for greater home integration.
- Reliable Performance:** Features ultra-reliable performance through a robust and dedicated mesh network Multiple Collections & Color Options: Choose from either the adorne® or radiant® collection to fit a home's unique needs. Additional color options available with use of Smart Lighting with Netatmo Color Change Kits
- Available in a range of contemporary colors and finishes. Coordinate with other designer Screwless Wall Plate Included:** Includes a radiant® wall plate in the box. switches & outlets.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007446777
Country Of Origin	China	Material	Polycarbonate
Features	Smart Lighting, With Netatmo	Switch Type	Button

Number of Switches	1	Works With	Amazon Alexa, Apple Home Kit, Google Home
Application Sector	Commercial, Multi-Dwelling Unit, Residential	Wall Plate Included	Yes
Standard	UL, cULus, FCC, ICC	Warranty Type	1-Year Limited Warranty
Type	Controller		

Dimensions

Product Width US	1.81 in	Product Weight US	0.159 lb
Product Depth US	1.11 in	Product Height US	1.5 in
Product Length US	4.78 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Additional Information

RoHS Compliant	Yes		
----------------	-----	--	--

Technical Information

Connection Location	Back Only	Terminal Accommodation	#14 AWG - #12 AWG
Connection	Wired	Number of Gangs	1
Amperage	0.1 A	Number of Poles	Multi-Location
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Mounting Type	In-Wall	Wire Connection Type	Internal Terminal Screw
Voltage	120 VAC		