




adorne Collection
adorne® Wireless Smart Switch with Netatmo, Graphite
Part No. WNAL23G1



Pair this softTap® battery-operated smart light switch with an adorne Smart Switch with Netatmo then add to any wall to control the same light from an additional location – no wires or tools needed. Use the included adhesive to mount anywhere in minutes. Perfect for rooms not wired for 3-way control. Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, adorne® with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, smart dimmer switches and smart outlets to build a solution that perfectly fits any space and need. Made exclusively for use with Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Smart Gateway REQUIRED. Must also be paired with an adorne or radiant Smart Switch with Netatmo or a Smart Plug-In Switch with Netatmo.

Perfect solution for adding 3-way control when paired with a Smart Switch with Netatmo.

Installs easily, without wires or cutting, for ultimate flexibility. Simply mount to any wall for long-lasting, battery-powered control.

Part of the adorne with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets (including wireless switches and dimmers).

Features ultra-reliable performance through a robust and dedicated mesh-network. (Established by the Smart Gateway.)

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

| | | | |
|--------------------|--|-------------------|--|
| Product Line | Pass & Seymour | Color | Graphite |
| Finish | Matte | Country Of Origin | China |
| Features | Smart Lighting, Wireless, With Netatmo | Switch Type | Touch |
| Number of Switches | 1 | Works With | Amazon Alexa, Apple Home Kit, Google Assistant |
| Application Sector | Commercial, Residential | Warranty Type | 1-Year Limited Warranty |

| | |
|------|--------|
| Type | Switch |
|------|--------|

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.79 in | Product Depth US | 0.24 in |
|------------------|---------|------------------|---------|

| | |
|-------------------|---------|
| Product Height US | 4.68 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E95219 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

| | |
|---------------|-----|
| FCC Compliant | Yes |
|---------------|-----|

Additional Information

| | |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

Technical Information

| | | | |
|-------------|---|---------------|---|
| Load Rating | Incandescent, halogen 1800W, Ballast 15A standard, electronic, LED 5A, 1/2 HP motor | Compatibility | Amazon Alexa, Apple HomeKit, Google Assistant |
|-------------|---|---------------|---|

| | | | |
|----------|------|-----------------|----------------|
| Amperage | 15 A | Number of Poles | Multi-Location |
|----------|------|-----------------|----------------|

| | | | |
|----------------|---------|---------|---------|
| Supply Voltage | 120 VAC | Voltage | 120.0 V |
|----------------|---------|---------|---------|

| | | | |
|-----------------|-------|-----------|-------------------------------|
| Connection Type | Wired | Load Type | Incandescent, Halogen, or LED |
|-----------------|-------|-----------|-------------------------------|
