



Pair this battery-operated sofTap® dimmer with an adorne Smart Tru-Universal Dimmer with Netatmo then add to any wall to control the same light from an additional location – no wires or tools needed. Use the included adhesive to mount anywhere in minutes. Perfect as a remote dimmer switch in rooms not wired for 3-way control. Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, adorne® with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, smart dimmer switches and smart outlets to build a solution that perfectly fits any space and need. Made exclusively for use with Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Smart Gateway REQUIRED. Must also be paired with an adorne or radiant Smart Tru-Universal Dimmer with Netatmo or a Smart Plug-In Tru-Universal Dimmer with Netatmo.

Installs easily, without wires or cutting, for ultimate flexibility. Simply mount to any wall for long-lasting, battery-powered control.

Features ultra-reliable performance through a robust and dedicated mesh-network. (Established by the Smart Gateway.)

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Perfect solution for adding 3-way control, no wiring required, when paired with a Smart Tru-Universal Dimmer with Netatmo.

Part of the adorne with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets (including other wireless switches and dimmers).

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

Product Line	Pass & Seymour	Color	Graphite
Finish	Matte	Country Of Origin	China
Features	Smart Lighting, Wireless, With Netatmo	Switch Type	Touch

Number of Switches	1	Works With	Amazon Alexa, Apple Home Kit, Google Assistant
--------------------	---	------------	--

Application Sector	Commercial, Residential	Standard	RoHS, cULus
--------------------	-------------------------	----------	-------------

Warranty Type	1-Year Limited Warranty	Type	Dimmer
---------------	-------------------------	------	--------

Dimensions

Product Width US	1.79 in	Product Depth US	0.24 in
------------------	---------	------------------	---------

Product Height US	4.68 in		
-------------------	---------	--	--

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E95219	cULus Listed	Yes
---------------------	--------	--------------	-----

FCC Compliant	Yes		
---------------	-----	--	--

Additional Information

RoHS Conformant	Yes		
-----------------	-----	--	--

Technical Information

Compatibility	Amazon Alexa, Apple HomeKit, Google Assistant	Electrical Rating	120V 1100W (Halogen), 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 2000W (Incandescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 8A (EFL)
---------------	---	-------------------	---

Connection	Wireless	Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon
------------	----------	--------------------	---

Number of Poles	Multi-Location	Indoor/Outdoor	Indoor
-----------------	----------------	----------------	--------

Supply Voltage	3 VDC	Environmental Conditions	95% (relative humidity, non-condensing)
----------------	-------	--------------------------	---