




adorne Collection
adorne® Wireless Smart Dimmer with Netatmo, Graphite
Part No. WNAL63G1



Pair this battery-operated sofTap® dimmer with an adorne Smart Tru-Universal Dimmer with Netatmo then add to any wall to control the same light from an additional location – no wires or tools needed. Use the included adhesive to mount anywhere in minutes. Perfect as a remote dimmer switch in rooms not wired for 3-way control. Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, adorne® with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, smart dimmer switches and smart outlets to build a solution that perfectly fits any space and need. Made exclusively for use with Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Smart Gateway REQUIRED. Must also be paired with an adorne or radiant Smart Tru-Universal Dimmer with Netatmo or a Smart Plug-In Tru-Universal Dimmer with Netatmo.

Installs easily, without wires or cutting, for ultimate flexibility. Simply mount to any wall for long-lasting, battery-powered control.

Features ultra-reliable performance through a robust and dedicated mesh-network. (Established by the Smart Gateway.)

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Perfect solution for adding 3-way control, no wiring required, when paired with a Smart Tru-Universal Dimmer with Netatmo.

Part of the adorne with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets (including other wireless switches and dimmers).

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

Product Line	Pass & Seymour	Color	Graphite
Finish	Metallic	UPC Number	785007381368
Country Of Origin	China	Features	Locator Light, Smart Lighting, Wireless, With Netatmo
Switch Type	Multi-Location, sofTap	Number of Switches	1

Works With	Amazon Alexa, Apple Home Kit, Google Assistant	Application Sector	Hospitality, Residential
Standard	RoHS, cULus	Warranty Type	2-Year Limited
Type	Dimmer		
Dimensions			
Product Width US	1.79 in	Product Depth US	0.24 in
Product Height US	4.68 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E95219	cULus Listed	Yes
FCC Compliant	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Seismic Tested	No	Dimming Compatibility	Wireless
Frequency Rating	2.4 to 2.4835 GHz	Number of Gangs	1
Number of Poles	Multi-Location	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Surface Mount, Wall Box	Wire Connection Type	Battery Powered
Voltage	3.0 V	Environmental Conditions	95% (relative humidity, non-condensing)