




adorne Collection
adorne® 15A Smart Outlet with Netatmo Plus-Size, Magnesium
 Part No. WNAR153M1



With this 15A smart outlet, take control lamps or small appliances from anywhere. (One outlet is app-controlled, the other is always on.) Monitor and manage energy usage through the app to reduce utility cost and waste. Part of the adorne® with Netatmo solution.

Smart Lighting lets you control lights and power, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, adorne® with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, dimmers and outlets to build a solution that perfectly fits a home's unique space and needs. Options even include wireless smart switches and dimmers for easily adding 3-way control.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Smart Gateway REQUIRED.

Installs easily in place of an existing 15A outlet. Can be wired to extend control to all outlets downstream or load-side. One outlet is app-controlled, the other is always on.

Part of the adorne with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets.

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Enables control of lamps or appliances via smartphones and tablets using the Legrand Home + Control app. Schedule them to turn on/off automatically, create groups, set scenes and monitor energy usage.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with black "invisi-shutters" for an invisible effect.

Features ultra-reliable performance through a robust and dedicated mesh-network. (Established by the Smart Gateway.)

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	Country Of Origin	China

Receptacle Type	5-15R	Number of Receptacles	2
-----------------	-------	-----------------------	---

Features	With Netatmo	Works With	Amazon Alexa, Apple Home Kit, Google Assistant
----------	--------------	------------	--

Outlet Type	Tamper-Resistant	Package Quantity	1
-------------	------------------	------------------	---

Application Sector	Residential/Commercial	Standard	RoHS, FCC, IC, cULus, UL
--------------------	------------------------	----------	--------------------------

Type	Outlet, Tamper-Resistant
------	--------------------------

Dimensions

Product Width US	1.73 in	Product Depth US	1.53 in
------------------	---------	------------------	---------

Product Height US	4.19 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E472890	cULus Listed	Yes
---------------------	---------	--------------	-----

FCC Compliant	Yes
---------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Is Tamper-Resistant	Yes	Number of Wires	2
---------------------	-----	-----------------	---

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

Number of Poles	Double Pole	Is Weather Resistant	No
-----------------	-------------	----------------------	----

Indoor/Outdoor	Indoor	Mounting Type	Box
----------------	--------	---------------	-----

Voltage	125.0 V	Connection Type	Wired
---------	---------	-----------------	-------

Environmental Conditions	95% (relative humidity, non-condensing)
--------------------------	---
