



Pair this battery-operated, wireless dimmer with a radiant Smart Tru-Universal Dimmer with Netatmo, then add it to any wall to control the same light from an additional location. No wires or tools needed. Use the included adhesive to mount anywhere in minutes. Perfect as a remote dimmer switch in rooms not wired for 3-way control. Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, radiant® with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, smart dimmer switches and smart outlets to build a solution that perfectly fits any space and need. Screwless Wall Plates from the radiant® Collection included.

## Features & Benefits

Smart Gateway REQUIRED. Must also be paired with an adorne or radiant Smart Tru-Universal Dimmer with Netatmo or a Smart Plug-In Tru-Universal Dimmer with Netatmo.

Installs easily, without wires or cutting, for ultimate flexibility. Simply mount to any wall for long-lasting, battery-powered control.

Features ultra-reliable performance through a robust and dedicated mesh-network. (Established by the Smart Gateway.)

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Perfect solution for adding 3-way control, no wiring required, when paired with a Smart Tru-Universal Dimmer with Netatmo.

Part of the radiant with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets (including other wireless switches and dimmers).

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems.

Screwless Wall Plate included. Coordinate with other designer switches and outlets available from the radiant® Collection for a cohesive, sophisticated look

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	Country Of Origin	China
Features	Smart Lighting, Wireless, With Netatmo	Switch Type	Paddle

Number of Switches	1	Works With	Amazon Alexa, Apple Home Kit, Google Assistant
--------------------	---	------------	--

Application Sector	Commercial, Residential	Warranty Type	1-Year Limited Warranty
--------------------	-------------------------	---------------	-------------------------

Type	Dimmer
------	--------

### Dimensions

Product Width US	1.73 in	Product Height US	4.19 in
------------------	---------	-------------------	---------

Product Length US	1.53 in
-------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E95219	cULus Listed	Yes
---------------------	--------	--------------	-----

FCC Compliant	Yes
---------------	-----

### Additional Information

RoHS Conformant	Yes	Product Has Potential to Contribute to LEED	Yes
-----------------	-----	---	-----

### Technical Information

Compatibility	Amazon Alexa, Apple HomeKit, Google Assistant	Electrical Rating	120V 1100W (Halogen), 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 2000W (Incandescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 8A (EFL)
---------------	---	-------------------	---

Actuator	Paddle	Connection	Wireless
----------	--------	------------	----------

---

Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon	Dimmer	Tru-Universal
--------------------	---	--------	---------------

---

Number of Poles	Multi-Location	Voltage	120.0 V
-----------------	----------------	---------	---------

---