




Wiremold
Sit Stand Desk Power 2 Receptacle 65W USB-C On-Desk, with 4 Receptacles Below Desk, White
Part No. SS24665WH

Purpose-built Sit-Stand Desk Power System delivering high-capacity on- and under-desk power, featuring 2 on-desk receptacles, 3 USB charging ports (2 USB-C and 1 USB-A w/ 65W shared charging), and 4 or 6 below-desk receptacles, available in Black or White



Features & Benefits

High-speed 65W USB-C charging: Up to 65W of USB-C power charges laptops from 0–50% in as little as 45 minutes

Fast, hassle-free installation: The desktop charging module securely clamps to the work surface (no screws required), while the under-desk power strip installs with just two screws (included).

Intelligent, safe charging: USB-C Power Delivery automatically communicates with connected devices to deliver the optimal voltage and current for fast, efficient charging. Built-in thermal management helps protect connected devices from overheating.

At-a-glance charging status: An integrated LED indicator eliminates the guesswork – yellow indicates charging in progress, while green signals the connected device is fully charged.

Designed for all sit-stand workstations: Compatible with the full range of standard sit-stand desk height adjustments, ensuring reliable power as your workspace moves.

Convenient desktop and under-desk power: Provides easy access to USB charging and AC power with 2 USB-C ports, 1 USB-A port, 2 tamper-resistant receptacles, and a choice of 4 or 6 under-desk receptacles for connected devices and peripherals

Built to withstand spills: UL 962A Spill Water Compliant, making it suitable for installation on horizontal work surfaces where accidental spills can occur.

Future-ready USB-C connectivity: High-power 65W USB-C charging supports today's laptops, tablets and smartphones providing a modern charging solution designed to accommodate tomorrow's workplace technology.

Specifications

General Info

Product Line	Wiremold	Color	White
UPC Number	786776201062	Country Of Origin	Mexico
Material	Plastic	Product Series	Sit Stand Desk Power
Number of Receptacles	6	Features	USB-A Charging, USB-C Charging
Outlet Type	Tamper-Resistant	Application Sector	Commercial, Residential
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Desktop Power Center

Dimensions

Product Width US	2.0 in	Product Height US	2.25 in
------------------	--------	-------------------	---------

Product Length US	14.4 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

ETL Listed	Yes	ETL ListingNumber	104599438CRT-001
------------	-----	-------------------	------------------

Additional Information

Energy Savings	No
----------------	----

Technical Information

USB Wattage	65 W	USB Amperage	3.25 A
Wiring Configuration	Single Circuit	Cord Length	6 ft
Number of USBs	3	Amperage	15 A
Wiring Method	Cord-ended	NEMA Configuration Code	5-15R
Mounting Type	On Surface	Power Delivery	65 W
Voltage	125.0 V		