



radiant Collection
radiant® Smart 15A Outlet with Netatmo, Nickel
Part No. WNRR15NI



With this 15A smart outlet, take control lamps or small appliances from anywhere. (One outlet is app-controlled, the other is always on.) Monitor and manage energy usage through the app to reduce utility cost and waste. Part of the radiant® with Netatmo solution. Smart Lighting lets you control lights and power, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, radiant® with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, dimmers and outlets to build a solution that perfectly fits a home's unique space and needs. Options even include wireless smart switches and dimmers for easily adding 3-way control. Screwless Wall Plates from the radiant® Collection included.

Features & Benefits

Smart Gateway REQUIRED.

Installs easily in place of an existing 15A outlet. Can be wired to extend control to all outlets downstream or load-side. One outlet is app-controlled, the other is always on.

Part of the radiant with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets.

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems.

Screwless Wall Plate included. Coordinate with other designer switches and outlets available from the radiant® Collection for a cohesive, sophisticated look

Enables control of lamps or appliances via smartphones and tablets using the Legrand Home + Control app. Schedule them to turn on/off automatically, create groups, set scenes and monitor energy usage.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with black "invisi-shutters" for an invisible effect.

Features ultra-reliable performance through a robust and dedicated mesh-network. (Established by the Smart Gateway.)

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

| | | | |
|-----------------------|----------------|-----------------|--------------|
| Product Line | Pass & Seymour | Color | Nickel |
| Finish | Matte | UPC Number | 785007289602 |
| Country Of Origin | China | Receptacle Type | 5-15R |
| Number of Receptacles | 2 | Features | With Netatmo |

| | | | |
|--------------------|--|-------------|-------------------------------|
| Works With | Amazon Alexa, Apple Home Kit, Google Assistant | Outlet Type | Tamper-Resistant, Wi-Fi Ready |
| Application Sector | Residential | Standard | RoHS, FCC, IC, cULus, UL |
| Warranty Type | 1-Year | Type | Outlet, Tamper-Resistant |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E472890 | cULus Listed | Yes |
| FCC Compliant | Yes | | |

Additional Information

| | | | |
|----------------|-----|---|-----|
| RoHS Compliant | Yes | Product Has Potential to Contribute to LEED | Yes |
|----------------|-----|---|-----|

Technical Information

| | | | |
|----------------------|------|---------------------|-------------|
| Seismic Tested | No | Is Tamper-Resistant | Yes |
| Number of Wires | 2 | Number of Gangs | 1 |
| Amperage | 15 A | Number of Poles | Double Pole |
| Is Weather Resistant | No | Indoor/Outdoor | Indoor |
| Mounting Type | Box | Connection Type | Wired |