PASS & SEYMOUR®

UL Fed Spec USB Chargers
15 & 20A, 125V

Charge ahead with the UL Fed Spec Grade USB duplex receptacle.

TR5262USB, TR5362USB

Pass & Seymour® Fed Spec Tamper-Resistant Duplex Receptacles with USB Charging capabilities are designed with strength and durability in mind. They were designed for the commercial market, and are capable of withstanding heavy use due to their UL Federal Specification certification. This product features an improved overall 3.1A USB charging capability, auto-ground clips, zinc-plated ground terminal screw, as well as triple-wipe brass contacts for lasting retention. The screw-pressure-plate back wiring makes installation fast and easy.

Features & Benefits

Overall 3.1A USB charging capability – combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 and 3.0 compatible devices

AC receptacles available in 15 and 20A, 125V

AC receptacles are tamper-resistant as standard – patented shutter system prevents improper insertion of foreign objects

Multiple color options available

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire

Stainless steel auto-ground clips assure positive ground

TR5262USBLA

3rd Party Compliance

c UL us LISTED

cULus Listed, UL Fed Spec Listed
Complies with test requirements UL 498, UL 1310, Fed Spec WC596, CSA C22.2 No. 42, CSA C22.2 No. 223

Ordering Information

Performance	
Electrical	
Dielectric Withstand Voltage	Withstands 1500V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)
Mechanical	
Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire
Product Identification	Ratings are a permanent part of device
Environmental	
Flammability	UL94 V2 (for device cover) 5V (for device body and frame)
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact

Materials	
Face	Polycarbonate
Body	Nylon
Contacts	CDA 260 Brass
Mounting Strap	.046" Zinc-Plated Brass
Terminal Screws	Tri-Drive Zinc-Plated Steel with Either Clear or Black Chromate For Color Identification
Ground Screw	Tri-Drive Steel with Green Chromate
Mounting Screws	Tri-Drive Steel
Auto-Ground Clip	Stainless Steel



Warranty
1 Year

Ordering Information

Duplex Tamper-Resistant Receptacle with USB Charger

Catalog Number	Rating A	V	Color	NEMA Configuration No.
TR5262USB	15A	125V	Brown	5-15R
TR5262USBW	15A	125V	White	5-15R
TR5262USBLA	15A	125V	Light Almond	5-15R
TR5262USBI	15A	125V	Ivory	5-15R
TR5262USBBK	15A	125V	Black	5-15R
TR5262USBGRY	15A	125V	Gray	5-15R
TR5262USBRED	15A	125V	Red	5-15R
TR5262USBGN	15A	125V	Green	5-15R
TR5262USBNI	15A	125V	Nickel-Plated	5-15R
TR5362USB	20A	125V	Brown	5-20R
TR5362USBW	20A	125V	White	5-20R
TR5362USBLA	20A	125V	Light Almond	5-20R
TR5362USBI	20A	125V	Ivory	5-20R
TR5362USBBK	20A	125V	Black	5-20R
TR5362USBGRY	20A	125V	Gray	5-20R
TR5362USBRED	20A	125V	Red	5-20R
TR5362USBGN	20A	125V	Green	5-20R
TR5362USBNI	20A	125V	Nickel-Plated	5-20R

NEMA 5-15R



NEMA 5-20R

Vertical Markets

- **Healthcare**
- **Hospitality/Lodging**
- **Education**
- **Office**
- **Airports**
- **Institutional**
- **Retail**
- **Multiple Dwelling**

Also available

- **Hospital Grade Devices**
- **SPD & Isolated Ground Devices**
- **Ground Continuity Monitoring (GCM)**
- **Straight Blade Plugs & Connectors**
- **Turnlok® Locking Devices**
- **Weatherproof Boxes & Covers**
- **IEC 309 Industrial Products**
- **Flexcor® Wire Mesh Grips**
- **Bulk Solutions**

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

905.738.9195
www.legrand.ca

FOLLOW US

SF20136 March 2018 **©2018 Legrand All Rights Reserved**