



Simplifying Installation and Improving Wire Acceptance

Backed by 130 years of innovation, Legrand now has a full line of residential electrical wiring devices that accept up to 10-gauge wire, including Copper-Clad Aluminum wire.

The line of switches, outlets and weather-resistant receptacles offer home builders and electricians everything needed to outfit a home's lighting controls and outlets.



Marking on Device & Packaging



- Easy to find marking reduces headaches and potential job shut down.
- Inspectors can be confident that the proper devices are used for compliance and safety.



TREX Design Expedites Installation

- Installation is easier and quicker, eliminating the need to loop wire.
- Less time on the job = savings on labor costs and more efficient timelines.

Accepts Up To 10 AWG CCA Wire

- Provides flexibility on wire usage to accommodate jobsite needs.
- Accepts solid and stranded wires, Copper-clad aluminum and copper wire.

RESIDENTIAL CONTRACTOR/BUILDER CHEAT SHEET

PART NUMBER (ALL COLORS)	PRODUCT NAME	MARKED ON DEVICE & PACKAGING	TREX DESIGN	ACCEPTS UP TO 10 AWG CCA WIRE	COLORS
660WG	Trademaster® Grounding Toggle Switch, Single-Pole	✓		✓	BK, I, LA, W, -
663WG	Trademaster® Grounding Toggle Switch, 3-Way	✓		✓	BK, I, LA, W, -
664WG	Trademaster® Grounding Toggle Switch, 4-Way	✓		✓	BK, I, LA, W, -
3232TREX	TradeMaster® External Pressure Plated Duplex Receptacle	✓	✓	✓	BK, I, LA, W, -, GRY
3232TREXRW	TradeMaster® External Pressure Plated Duplex Receptacle, Weather-Resistant	✓	✓	✓	W, -, GRY, LA, I, BK
3232TRW	Trademaster® Duplex Receptacle	✓		✓	BK, I, LA, W, -
885TREXRW	radiant® External Pressure Plated Outlet, Weather-Resistant	✓	✓	✓	W, -, GRY, LA, I, BK
885TRW	radiant® Outlet	✓		✓	BK, I, LA, W, -, GRY, DB, G, N
CP498TR15	Kitchen Countertop Outlet, 15A	✓		✓	BK, W
CP498TR20	Kitchen Countertop Outlet, 20A	✓		✓	BK, W
TM870W	radiant® Single-Pole Switch	Coming Q3 2026		✓	BK, I, LA, W, -, GRY, DB, G, N
TM873W	radiant® 3-Way Switch	Coming Q3 2026		✓	BK, I, LA, W, -, GRY, DB, G, N
TM874W	radiant® 4-Way Switch	Coming Q3 2026		✓	BK, I, LA, W, -, GRY, DB, G, N
1597TRW	radiant® 15A Duplex Self-Test GFCI Receptacle	Coming Q3 2026		✓	BK, I, LA, W, -, GRY, DB, G, N
2097TRW	radiant® 20A Duplex Self-Test GFCI Receptacle	Coming Q3 2026		✓	BK, I, LA, W, -, GRY, DB, G, N
1597TRUSBACW	radiant® GFCI USB Outlet, Type A/C, 15A	Coming Q3 2026		✓	BK, I, LA, W, -, GRY
2097TRUSBACW	radiant® GFCI USB Outlet, Type A/C, 20A	Coming Q3 2026		✓	BK, I, LA, W, -, GRY
1597TRWRW	radiant® 15A Duplex Self-Test GFCI Receptacle, Weather-Resistant	Coming Q3 2026		✓	BK, I, LA, W, -, GRY
2097TRWRW	radiant® 20A Duplex Self-Test GFCI Receptacle, Weather-Resistant	Coming Q3 2026		✓	BK, I, LA, W, -, GRY
1597NLTTRW	radiant® 15A Duplex Self-Test GFCI Receptacle with Night Light	Coming Q3 2026		✓	DB, I, LA, N, W
TM826USBW	radiant® 3.1A USB Outlet, Type A, 15A	Coming Q3 2026		✓	BK, I, LA, W, G, N
R26USBACW	radiant® 3.1A USB Outlet, Type A/C, 15A	Coming Q3 2026		✓	DB, I, G, LA, N, W, B
R26USBAC6W	radiant® 15W USB Outlet, Type A/C, 15A	Coming Q3 2026		✓	BK, I, LA, W, G
R26USBCC6W	radiant® 15W USB Outlet, Type C, 15A	Coming Q3 2026		✓	BK, I, LA, W, G
R26USBPD65W	radiant® 65W USB Outlet, Type C, 15A	Coming Q3 2026		✓	BK, I, LA, W, -, GRY, DB, G, N
R26USBPDW	radiant® 30W USB Outlet, Type C, 15A	Coming Q3 2026		✓	BK, I, LA, W, -, GRY, DB, G, N
TR15USBACW	3.1A Spec Grade USB Outlet, Type A/C, 15A	Coming Q3 2026		✓	BK, I, LA, W, -, GRY
TR15USBAC6W	15W Spec Grade USB Outlet, Type A/C, 15A	Coming Q3 2026		✓	BK, I, LA, W, -, GRY
TR15USBCC6W	15W Spec Grade USB Outlet, Type C, 15A	Coming Q3 2026		✓	BK, I, LA, W, -, GRY
TR20USBPDW	30W Spec Grade USB Outlet, Type C, 20A	Coming Q3 2026		✓	BK, I, LA, W, -, GRY, DB, G, N, RED
TR20USBPD65W	65W Commercial USB Outlet, Type C, 20A	Coming Q3 2026		✓	BK, I, LA, W, -, GRY, DB, G, N, RED
TR53201W	TradeMaster Residential Single Outlet, 20A			✓	W
RRW600U	radiant® Single Pole 3-Way Occupancy Sensor			✓	TRI, BK, W
RRW600V	radiant® Single-Pole 3-Way Vacancy Sensor			✓	TRI, BK
RT2	radiant® 4-Button Digital Timer			✓	DB, I, LA, N, W, B
RHDH163P	radiant® Single Pole/3-Way Fan Speed Control			✓	TRI, BK, W
TSDDH163P	Toggle Slide De-Hummer Single Pole/3-Way			✓	BK, I, LA, W, GRY, RED