



**Wiremold**  
**Cord Ended deQuorum™ Dual Flip-Up Unit with USB**  
Part No. DQFP15UST-2A



Unit includes one (1) 15A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Second opening will accept adapter for one (1) Wiremold CM Series Open System 2A module, one (1) Ortronics Series II or one (1) TracJack adapter to accommodate a wide range of communication outlets. Adapters are included in hardware bag. Unit comes with a 6' (1.83m) cord. Comes with a brushed stainless steel finish.

## Features & Benefits

**Sleek, Attractive Design:** Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

**Tamper-Resistant Receptacles:** Meets 2011 NEC TamperResistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

**New Soft Opening Cover Mechanism:** Opening and closing the cover is quieter and easier with a more professional feel.

**Expanded Configuration Options:** Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

**UL Spill Water Protection:** Meets and exceeds UL1363 standard for relocatable power taps. Eliminates risk of shock or short circuiting due to moisture entering device.

**USB Charging Capability:** Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

**Multiple Cover Finish Options:** Durable black powder coat and brushed stainless steel finishes blend with most decors.

**cULus Listed:** Meets UL US and Canadian safety standards for Relocatable Power Taps (File E66421, Guide XYBS) and Multitoutlet Assemblies (File E15191, Guide PVGT).

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776184570
Country Of Origin	Mexico	Construction	Die Cast
Application Sector	Residential/Commercial	Standard	cULus Listed Relocatable Power Tap: File E66421 Guide XYBS, cULus Listed Multioutlet Assembly: File E15191 Guide PVGT, Meets Article 380 of NEC
Type	Flip Up		

### Dimensions

---

Product Width US	4.75 in	Product Length US	10.812 in
------------------	---------	-------------------	-----------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Buy American Act Compliance

---

NAFTA	Yes
-------	-----

---

### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

### Technical Information

---

Cable Entry	Below	Mounting Type	Recessed
-------------	-------	---------------	----------

---

Number of Outlets	2
-------------------	---

---