



adorne Collection  
adorne® Whisper® Tru-Universal Dimmer, Graphite, with Microban®  
Part No. ADWR703TUG4



The whisper-control modern dimmer switches from the adorne Collection allow you to control lights with a soft, fluid motion. Integral silver contacts provide long-lasting performance. A self-calibrating Tru-Universal Dimmer, this dimmer switch works with virtually any 120V dimmable bulb or fixture (excludes 0-10V).

This dimmer\* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

\* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box; neutral wire required.

Works with virtually any 120V dimmable bulb or fixture (excludes 0-10V).

Usable in both single-pole and 3-way applications.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Control lights with a fluid, whisper-soft toggle motion to turn on/off, or use the smooth slider to dim or brighten to your preferred light level.

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Graphite
Country Of Origin	China	Features	Antimicrobial Protection
Switch Type	Whisper	Number of Switches	1

Warranty Type	Limited Lifetime Warranty
---------------	---------------------------

Dimensions

Product Width US	1.77 in	Product Depth US	1.2 in
Product Height US	4.19 in		

Technical Information

Electrical Rating	120V 1100W (Halogen), 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 2000W (Incandescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 8A (EFL)	Number of Gangs	1
Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon	Number of Poles	3-Way, Single Pole
Wattage	700 W	Mounting Type	Box
Voltage	120.0 V	Connection Type	Internal Pressure Plates