




adorne Collection
adorne® Paddle Switch, Half-Size, White, with Microban®
Part No. ASPD1531W4



With its twist on classic up-and-down switch control, this modern light switch lets you turn lights on and off with ease and style. Use the light switch on its own to control a light or fixture from a single location, or pair with a second switch or dimmer to control a single light source from two locations. Combine this half-size switch with other half or standard-sized devices to fit more functionality in a single Wall Plate.

This switch* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Combine with another half or standard-sized device to fit into a 1-Gang or 1-Gang+ Wall Plate.

Specifications

General Info

| | | | |
|-------------------|----------------|-------------------------|--------------------------|
| Product Line | Pass & Seymour | Replaced by Part Number | |
| Color | White | Finish | Matte |
| Country Of Origin | China | Features | Antimicrobial Protection |
| Switch Type | Paddle | Number of Switches | 1 |

| | | | |
|----------|-------|---------------|---------------------------|
| Standard | cULus | Warranty Type | Limited Lifetime Warranty |
|----------|-------|---------------|---------------------------|

Dimensions

| | | | |
|------------------|--------|------------------|---------|
| Product Width US | 1.5 in | Product Depth US | 0.89 in |
|------------------|--------|------------------|---------|

| | |
|-------------------|---------|
| Product Height US | 1.77 in |
|-------------------|---------|

Technical Information

| | | | |
|------------|-----------------|-----------------|---|
| Connection | Screw Terminals | Number of Gangs | 1 |
|------------|-----------------|-----------------|---|

| | | | |
|----------|------|-----------------|--------------------|
| Amperage | 15 A | Number of Poles | 3-Way, Single Pole |
|----------|------|-----------------|--------------------|

| | | | |
|---------------|-----|---------|---------|
| Mounting Type | Box | Voltage | 120.0 V |
|---------------|-----|---------|---------|

| | |
|-----------------|--------------------------|
| Connection Type | Internal Pressure Plates |
|-----------------|--------------------------|
