



Outdoor charging station with an LED accent light to enable device charging during the day and after dark. Accent light ensures the station stands out from standard bollards and clearly indicates charging. Station includes one duplex GFCI Receptacle and one 4-Port USB Outlet.

Features & Benefits

- Charging & Illumination - Combine power with area lighting in one pedestal to maximize functionality of outdoor spaces.**
- Outdoor-Rated Construction – Rugged aluminum form designed for durability in all weather conditions. UL listed to NEMA 3R requirements to ensure optimal performance.**
- Durable, Premium Finishes – Available in three outdoor-rated finishes to complement your space design. Choose from black, bronze or silver.**
- A/V & Communication Compatible – Add an A/V-Communication Kit to 3-gang versions to accommodate Wiremold AVIP plates as well as decorator A/V or communication devices. Enables pedestal to support outdoor presentation areas and classrooms, eliminating the need to bring cables from inside a building.**
- Device Shelves – Add up to two pairs of shelves to hold mobile devices while charging.**
- Door Options – Interior illuminates when door is open. Replace standard color-matched door with a transparent version to make devices inside more visible. Or, select a lockable door for added security or to ensure use is limited to facility personnel.**

Specifications

General Info

| | | | |
|-----------------------|-------------------|-------------------|---|
| Product Line | Wiremold | Color | Bronze |
| UPC Number | 786776185829 | Country Of Origin | Mexico |
| Number of Receptacles | 1 | Features | USB-A Charging |
| Application Sector | Commercial | Standard | cULus Listed, File Number E479489, Guide PUPR |
| Type | Charging Stations | Installed Devices | 4-Port USB-A, GFCI |

Dimensions

| | | | |
|------------------|--------|-------------------|--------|
| Product Width US | 6.0 in | Product Weight US | 6.0 lb |
|------------------|--------|-------------------|--------|

| | | | |
|-------------------|---------|-------------------|--------|
| Product Height US | 46.5 in | Product Length US | 8.0 in |
|-------------------|---------|-------------------|--------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E479489 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Buy American Act Compliance

| | |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

Additional Information

| | | | |
|-----------------|-----|-------------------------------|-----|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |
|-----------------|-----|-------------------------------|-----|

Technical Information

| | | | |
|--------------|-----|----------------|---|
| Is Pre-Wired | Yes | Number of USBs | 4 |
|--------------|-----|----------------|---|

| | | | |
|-----------------|---|----------|------|
| Number of Gangs | 2 | Amperage | 20 A |
|-----------------|---|----------|------|

| | |
|----------------|--------------|
| Lighting Types | Accent Light |
|----------------|--------------|
