



Pass and Seymour
PlugTail® Commercial Passive Infrared (PIR) Wall Switch Sensor, White
Part No. PTWSP250W



Features & Benefits

- Detection Signature Analysis provides high immunity to RFI and EMI. Integrated light level sensor works from 10 to 150 footcandles.
 - Compatible with all electronic and magnetic ballasts, PL lamp ballasts, compact fluorescent. Adjustable time delay of 30 seconds to 30 minutes.
 - Dual 120/277VAC operation, Adjustable sensitivity from 20% to 100%, 180 degree coverage of up to 900 sq. ft. Patented voltage drop protection and zero crossing circuitry.
 - No exposed terminals create a fingersafe application before, during, and after installation. Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- For covering patents, see www.legrand.us/patents. :

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	WS-301-W
Color	White	Country Of Origin	Mexico
Application Sector	Commercial/Industrial	Standard	CSA Listed, cULus, UL Listed

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Target Size	180 deg	Response Frequency	60 Hz
Sensor Type	Occupancy	Sensing Range	900 sq ft
Sensitivity	60Hz	Load	120/277VAC
Environmental Conditions	Indoor Use Only		