



802.11n In-Wall/Ceiling Wireless Access Point



One part number, two installation options



802.11n technology provides ultra-high-speed wireless with improved range and expanded coverage area

DA1101
In-Wall/Ceiling Wireless Access Point

INNOVATIVE TECHNOLOGY

Integrating the latest in wireless technology, the 802.11n Wireless Access Point (N-WAP) provides high-performance functionality for flexible wireless communication. With built in IEEE 802.11b/g/n wireless network capability, the N-WAP allows any computer and wireless-enabled network client to connect without additional cabling.

The N-WAP is supplied with mounting hardware for two different installation methods. It can be mounted in a three-gang electrical box using the round cover for in-ceiling installation, or in a single-gang electrical box using the small rectangular cover for in-wall installation. The N-WAP is unobtrusive in look similar to an in-wall speaker or smoke detector, letting it blend right in to any décor.



PRODUCT FEATURES

- Backwards compatible with the 802.11b/g standard (11Mbps/54Mbps)
- Unique design allows for in-ceiling or on-wall mounting
- User-friendly web-based GUI for configuration and management purposes
- Offers data speeds of up to 300Mbps
- Two antennas for greater coverage
- Defaults to AP mode with no configuration required, but also supports wireless client mode and AP + client mode



www.legrand.us/onq



802.11n In-Wall/Ceiling Wireless Access Point

RELATED PRODUCTS



DA1002
5-Port 10/100 Base-T
Ethernet Switch Module



DA1004
4-Port Ethernet
Router/Switch




DA1008
8-Port Gigabit Switch

PRODUCT SPECIFICATIONS

Mounting	In-Wall / In-Ceiling
Bracket Included	Yes
Power Supply Included	Yes
Power Requirements	48 VDC 250 MA (Midspan)
Operating Temperature	0° to 55° C
Storage Temperature	-20° to 70° C
Humidity	Up to 95% RH (Non-Condensing)
Signal Type	11b mode: DSSS 11g mode: OFDM 11n mode: OFDM, MIMO
Modulation	11b mode: CCK, DQPSK, DBPSK 11g mode: 64 QAM, 16 QAM, QPSK, BPSK 11n mode: 64 QAM, 16 QAM, QPSK, BPSK
LAN Port	1 x 10/100, Auto-MDI/MDI-X
Antennas	2 x embedded antenna
Data Encryption	64 bit / 128 bit WEP, WPA-PSK, WPA2-AES, WPA, WPA2
Frequency	2.4GHz - 2.484GHz
Data Rate	11b mode: 1/2/5.5/11Mbps 11g mode: 6/9/12/18/24/36/48/54Mbps 11n mode: up to 300Mbps

WIRING DIAGRAM



301 Fulling Mill Road, Suite G
Middletown, PA 17057
(800) 321-2343



www.legrand.us/onq

©2012 by Legrand. All Rights Reserved.