


PASS & SEYMOUR® Hard Use Spec Grade Plug Load Controllable Receptacles

Durable receptacles designed for energy savings.

5262CH, 5362CH, 5262CD, 5362CD TR5262CH, TR5362CH, TR5262CD, TR5362CD

These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. The controlled receptacle marking printed on the face of the receptacle is both NEMA-approved and compliant with the National Electrical Code®, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1. This clear, permanent marking helps end-users differentiate controlled receptacles from others. Corrosion-resistant plated steel straps and highstrength nylon faces make these receptacles perfect for any hard use application. They feature one-piece, triple-wipe brass contacts for lasting retention. And screw-pressure-plate back wiring makes installation fast and easy.



- Controlled receptacle marking is NEMA-approved and compliant with 2017 NEC®, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.
- · Can be wired to any number of stand-alone or systembased plug load control solutions.
- CH Version Only: Split circuit tab broken at the factory, allowing half of the receptacle to be controlled.
- Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

3rd Party Compliance

c**(ŲL)**us UL Listed, File Number E140596, Standard UL498. Fed Spec WC596. CSA Certified File Number LR16063, Standard CSA-C22.2 No. 42 General Use Receptacles. Conforms to NEMA WD-1 and WD-6.



Features & Benefits




Technical Information

Electrical		
Dielectric Withstand Voltage	Withstands 2000V minimum	
Maximum Working Voltage	125V	
Current Interrupting	Certified for current interrupting at full-rated current	
Temperature Rise	Maximum 30°C temperature rise at full-rated curren after 50 cycles of overload at 150% of rated current with direct current	
Mechanical		
Terminal Identification	Terminal Identification in accordance with UL 498 (Brass, White, Green)	
Terminal Accommodation	#14 AWG - #10 AWG copper conductor only	
Product Identification	Ratings are permanent part of the device	
Environmental		
Flammability	UL94 V2	
Operating Temperature	Maximum continuous +60°C, minimum -40°C (without impact)	



Materials

Materials	
Face	Nylon
Back Body	PVC
Line Contacts	.032 688 Brass
Mounting Strap	.042" Zinc-Plated Steel
Ground Contacts	.040" 688 Brass
Pressure Plate	.080" Steel
Terminal Screws	#8 Tri-Drive Steel (Neutral = Nickel-Plated Steel)
Ground Screw	#8 Hex Tri-Drive Brass
Assembly Drive Screw	Zinc-Plated Steel
Auto-Ground Clip	Stainless Steel
Mounting Screws	Tri-Drive Steel
Ink	Pad Printed
Tamper-Resistant Shutters	Thermoplastic (for TR models)



TR5362CHBK

Warranty

1 Year

Llegrand[®]

PASS & SEYMOUR® Hard Use Spec Grade Plug Load

Controllable Receptacles

Ordering Information

Half-Controlled Duplex Receptacles Back & Side Wire

Catalog Number	Ratings	Color	NEMA Config.
5262CHI	15A 125V	lvory	5-15R
5262CHW	15A 125V	White	5-15R
5262CH	15A 125V	Brown	5-15R
5262CHGRY	15A 125V	Gray	5-15R
5262CHBK	15A 125V	Black	5-15R
5262CHLA	15A 125V	Light Almond	5-15R
5262CHGN	15A 125V	Green	5-15R
5262CHBL	15A 125V	Blue	5-15R
5362CHI	20A 125V	lvory	5-20R
5362CHW	20A 125V	White	5-20R
5362CH	20A 125V	Brown	5-20R
5362CHGRY	20A 125V	Gray	5-20R
5362CHBK	20A 125V	Black	5-20R
5362CHLA	20A 125V	Light Almond	5-20R
5362CHGN	20A 125V	Green	5-20R
5362CHBL	20A 125V	Blue	5-20R

Dual-Controlled Duplex Receptacles Back & Side Wire NEMA


Catalog Number	Ratings	Color	NEMA Config.
5262CDI	15A 125V	lvory	5-15R
5262CDW	15A 125V	White	5-15R
5262CD	15A 125V	Brown	5-15R
5262CDGRY	15A 125V	Gray	5-15R
5262CDBK	15A 125V	Black	5-15R
5262CDLA	15A 125V	Light Almond	5-15R
5262CDGN	15A 125V	Green	5-15R
5262CDBL	15A 125V	Blue	5-15R
5362CDI	20A 125V	lvory	5-20R
5362CDW	20A 125V	White	5-20R
5362CD	20A 125V	Brown	5-20R
5362CDGRY	20A 125V	Gray	5-20R
5362CDBK	20A 125V	Black	5-20R
5362CDLA	20A 125V	Light Almond	5-20R
5362CDGN	20A 125V	Green	5-20R
5362CDBL	20A 125V	Blue	5-20R

Tamper-Resistant Half-Controlled Duplex Receptacles Back & Side Wire

Catalog Number	Ratings	Color	NEMA Config.
TR5262CHI	15A 125V	lvory	5-15R
TR5262CHW	15A 125V	White	5-15R
TR5262CHGRY	15A 125V	Gray	5-15R
TR5262CHLA	15A 125V	Light Almond	5-15R
TR5262CHBL	15A 125V	Blue	5-15R
TR5362CHI	20A 125V	lvory	5-20R
TR5362CHW	20A 125V	White	5-20R
TR5362CH	20A 125V	Brown	5-20R
TR5362CHGRY	20A 125V	Gray	5-20R
TR5362CHBK	20A 125V	Black	5-20R
TR5362CHLA	20A 125V	Light Almond	5-20R
TR5362CHBL	20A 125V	Blue	5-20R

Tamper-Resistant Dual-Controlled Duplex Receptacles Back & Side Wire

Catalog Number	Ratings	Color	NEMA Config.
TR5262CDI	15A 125V	lvory	5-15R
TR5262CDW	15A 125V	White	5-15R
TR5262CD	15A 125V	Brown	5-15R
TR5262CDGRY	15A 125V	Gray	5-15R
TR5262CDLA	15A 125V	Light Almond	5-15R
TR5262CDBL	15A 125V	Blue	5-15R
TR5362CDI	20A 125V	lvory	5-20R
TR5362CDW	20A 125V	White	5-20R
TR5362CD	20A 125V	Brown	5-20R
TR5362CDGRY	20A 125V	Gray	5-20R
TR5362CDBK	20A 125V	Black	5-20R
TR5362CDLA	20A 125V	Light Almond	5-20R
TR5362CDBL	20A 125V	Blue	5-20R




For more information on these and other P&S products refer to our Catalog or visit our web site.



PASS & SEYMOUR®

Hard Use Spec Grade Plug Load Controllable Receptacles

Plug Load Controllable Receptacles Wiring Diagram



Note: Hot conductors may be any color OTHER than white, gray or green.

Vertical Markets • Office • Institutional • MDU • Education • Hospitality/Lodging • Hospitalble... • USB Charging Devices • Ground Continuity Monitoring (GCM) • SPD & Isolated Ground Devices • Hospital Grade Devices • Straight Blade Plugs & Connectors • IEC 309 Industrial Products

- PlugTail[®] Wiring Devices
- Turnlok[®] Locking Devices
- Flexcor[®] Wire Mesh Grips

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America 60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us

Canada 905.738.9195 www.legrand.ca

