

Single-Pole, Double-Throw Switch, 20A, 120/277V



Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw only.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see <https://www.legrand.us/patents>.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit www.legrand.us/electrical-wiring-devices/wall-plates.

Specifications

General Info

| | | | |
|--------------------|----------------|--------------------|------------------------|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 785007122541 |
| Country Of Origin | Mexico | Material | Thermoplastic |
| Features | Durable | Switch Type | Toggle |
| Number of Switches | 1 | Application Sector | Commercial, Industrial |

| | | | |
|--|--|-----------------------|-------------------------------------|
| Wall Plate Included | No | Standard | UL listed |
| Warranty Type | 1-Year Limited Warranty | Type | Manual Controller, Tamper-Resistant |
| Dimensions | | | |
| Product Width US | 1.5 in | Product Depth US | 1.469 in |
| Product Height US | 3.281 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| CSA Listed | Yes | cULus ListingNumber | 31169 |
| cULus Listed | Yes | CSA File Number | 17949 |
| Technical Information | | | |
| Load Rating | 20 A @ 120/277 VAC | Connection Location | Back Only |
| Terminal Accommodation | #14 AWG - #10 AWG | Number of Gangs | 1 |
| Throw Type | Double Throw | Amperage | 20 A |
| Number of Poles | Single Pole | Requires Neutral Wire | Yes |
| Indoor/Outdoor | Indoor | Mounting Type | Wall Box |
| Wire Connection Type | Screw Terminals | Voltage | 120 VAC, 277 VAC |
| Load Type | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon | | |