



Pass and Seymour
SteriGuard™ Antimicrobial Straight Blade Plug 15A, 125V, Yellow
Part No. 14W47AM



SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure

Features & Benefits

UL and CSA Listed

NSF (National Sanitation Foundation)
Certified

Patent Pending

Anti-microbial Additives Embedded in
polymer and inhibits Growth of Bacteria,
Molds, Mildews and Fungi

Anti-microbial Additive Resistant to Scuffing and Cleaning

Escherichia (E.Coli): - Log reduction
greater than 4.8, reduces surface bacteria
by greater than 99.99%

Staphylococcus (Staph), MRSA: - Log Reduction greater than 4.3, reduces
surface bacteria by greater than 99.97%

Salmonella : Log Reduction Greater Than
3.6, reduces surface bacteria by Greater
Than 99.97%

RoHS Compliant (Non-Halogenated)

Independently tested and Certified to JIS
Z2801 standards

Resistant to High Pressure Hose-down applications

Tongue & Groove Environmental Sealing

Keyed Body and Cover for Alignment

NEMA Type 4, 4x, 6, 6P and IP67 Protection

SteriGuard: Anti-microbial Wiring Devices are ideal for a wide range of
applications including food and beverage preparation, procession, & packaging:
agriculture, pharmaceutical, and health care.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007056976	Country Of Origin	United States

Application Sector	Commercial	Standard	CSA Listed, FSUL, UL Listed
Dimensions			
Product Width US	1.85 in	Product Depth US	2.62 in
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes		
Technical Information			
Phase	Single	Connection	Cable
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 12 AWG
Environmental Conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized		