



Features & Benefits

- First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere

Rated for use in hospitals and healthcare facilities, this outlet offers superior durability and reliable ground fault protection. Includes a trip indicator light and reset button on the outlet for easy, accessible troubleshooting
- Includes traditional power outlets and two USB Type-C ports for convenient, future-proof charging. Shares 2.0A charging capacity between both ports

Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced
- Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection

Prevents the insertion of foreign objects while maintaining a discreet, invisible effect with patented, black "invisi-shutter" system. Meets NEC® Tamper-Resistant requirements
- Installs quickly thanks to a redesigned side wire cavity for easier access

Can provide ground fault protection to downstream outlets through feed-thru wiring

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Features	USB-C Charging
Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper-Resistant, USB-Charging	Application Sector	Residential/Commercial
Warranty Type	1-Year Limited Warranty	Type	Duplex, GFCI, Tamper-Resistant, USB

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	E140596
cULus Listed	Yes	CSA File Number	CSA C22.2 No. 223, CSA C22.2 No. 42

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Is Tamper-Resistant	Yes	USB Amperage	2.1 A
Number of USBs	2	Number of Gangs	1
Amperage	15 A	Is Weather Resistant	No
Indoor/Outdoor	Indoor	Wattage	1875 W
Mounting Type	Box	Voltage	125.0 V
