



Pass and Seymour
Portable 6-Foot In-Line 15A Self-Test GFCI with Straight Blade Plug and Connector, Manual Reset
Part No. 1597PC6M



The perfect option for safely powering portable equipment, outdoors or in, when a GFCI-protected outlet is not accessible. Use this 6-Foot In-Line Portable GFCI (Manual Reset) when plugging in drills, saws, leaf blowers, pressure washers, power painters, etc.

Ground-Fault Circuit Interrupters (GFCI) help prevent electrical shock caused by ground faults. GFCI protection is required by code in bathrooms, kitchens, garages, outdoor areas, and for any other outlets found within six feet of a sink or water source.

Features & Benefits

- Protects against electrical shock caused by ground-fault occurrences.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected.

Requires portable GFCI to be manually set for use by pressing reset button upon plug in and after loss of primary power.
- Conducts an industry-leading automatic self-test every 3 seconds. If the portable GFCI device ever fails, the red indicator light flashes to signal it should be replaced.

Open neutral relay automatically cuts power to device line conductor if the neutral wire preceding the portable GFCI becomes damaged.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Finish	Matte	UPC Number	785007381634
Country Of Origin	China	Outlet Type	GFCI
Application Sector	Commercial, Residential	Warranty Type	1-Year Limited Warranty
Type	Straight Blade		

Dimensions

Product Width US	2.0 in	Product Weight US	1.3 lb
Product Depth US	1.75 in	Product Length US	75.75 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	943	cULus Listed	Yes
---------------------	-----	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Seismic Tested	No	Is Tamper-Resistant	No
----------------	----	---------------------	----

Amperage	15 A	Is Weather Resistant	No
----------	------	----------------------	----

Indoor/Outdoor	Outdoor
----------------	---------
