



Wiremold
10AT Prewired Evolution™ Series Poke Thru Device, Surface Style Cover
Part No. 10ATCPBZ



For use with 10" (254mm) diameter hole. Cover and stem are pre-assembled together. All devices are recessed 4 1/2" (114mm) below the finished floor level. Unit ships complete with an all aluminum cover (assembled) designed to sit on top of finished floor surface (carpet, tile, wood, concrete or terrazzo). Covers are available in the following powder coated finishes: black (BK), gray (GY), nickel (NK), brass (BS) and aluminum (AL).

Features & Benefits

For use with 10" (254mm) diameter hole. Cover and stem are pre-assembled together. All devices are recessed 4 1/2" (114mm) below the finished floor level. Unit ships complete with an all aluminum cover (assembled) designed to sit on top of finished floor surface (carpet, tile, wood, concrete or terrazzo). Powder coated black finish.

Specifications

General Info

| | | | |
|--------------|---|--------------------|---------------|
| Product Line | Wiremold | Color | Bronze |
| UPC Number | 786564087120 | Country Of Origin | United States |
| Construction | Assembled | Application Sector | Commercial |
| Standard | cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT, cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY Meets Article 300.21 300.22[C] & 314 of NEC | Type | Poke-Thru |

Dimensions

Cubic Capacity 19 cu in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber E2961 cULus Listed Yes

Buy American Act Compliance

| | |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

Additional Information

| | | | |
|-----------------|-----|-------------------------------|-----|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |
|-----------------|-----|-------------------------------|-----|

Technical Information

| | | | |
|-------------|------------------------|-------------------|---|
| Cable Entry | conduit & pass through | Number of Outlets | 4 |
|-------------|------------------------|-------------------|---|
