



Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected. For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

## Features & Benefits

- Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI receptacles make it easier to fix trips with a reset button right on the device.
- Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.
- Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected.
- Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly.
- Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.
- Replaces any standard receptacle with ease, in as little as 10 minutes.
- Features durable, high-impact resistant thermoplastic construction.
- More color options available to fit any style, including finishes to match current hardware and lighting trends.
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

| General Info      |   |                       |                         |
|-------------------|---|-----------------------|-------------------------|
| Product Line      | Pass & Seymour                            | Color                 | Gray                    |
| Country Of Origin | Mexico                                    | Number of Receptacles | 2                       |
| Outlet Type       | GFCI, Indoor, Self-Test, Tamper-Resistant | Application Sector    | Residential/Commercial  |
| Standard          | cULus, UL Listed, FSUL                    | Warranty Type         | 1-Year Limited Warranty |

Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.73 in | Product Depth US | 1.03 in |
| Product Height US | 4.2 in  |                  |         |

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|                     |                    |                          |                        |
|---------------------|--------------------|--------------------------|------------------------|
| Is Tamper-Resistant | Yes                | Interrupt Rating         | 4 A                    |
| Frequency Rating    | 60 Hz              | Trip Range               | 5±1 mA                 |
| Connection          | Back and Side Wire | Number of Gangs          | 1                      |
| Amperage            | 15 A               | Mounting Type            | Box                    |
| Voltage             | 125.0 V            | Environmental Conditions | 95% Humidity, UL 94 V2 |