



Pass and Seymour
20A Single Pole, Double Throw Switch, White
Part No. 1225W

Single-Pole, Double-Throw Switch, 20A, 120/277V



Features & Benefits

| | |
|---|--|
| Oversize silver alloy contacts for long life and better heat dissipation. | Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors. |
| Fiber terminal insulation barriers standard. | Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures. |
| Bodies, covers, and toggles molded of durable nylon. | Single Pole-Double Throw only. |
| Locking Switches supplied with one 1498-NT key. | Normally open. |
| For covering patents, see https://www.legrand.us/patents . | For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit www.legrand.us/electrical-wiring-devices/wall-plates . |

Specifications

General Info

| | | | |
|--------------------|------------------------|---------------------|--------------|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 785007122541 |
| Country Of Origin | Mexico | Features | Durable |
| Switch Type | Toggle | Number of Switches | 1 |
| Application Sector | Commercial, Industrial | Wall Plate Included | No |

| | | | |
|---------------------------------------|--|-----------------------|-------------------------|
| Standard | UL listed | Warranty Type | 1-Year Limited Warranty |
| Type | Manual Controller, Tamper-Resistant | | |
| Dimensions | | | |
| Product Width US | 1.5 in | Product Depth US | 1.469 in |
| Product Height US | 3.281 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| CSA Listed | Yes | cULus Listed | Yes |
| CSA File Number | 17949 | | |
| Technical Information | | | |
| Load Rating | 20 A @ 120/277 VAC | Connection Location | Back Only |
| Terminal Accommodation | #14 AWG - #10 AWG | Number of Gangs | 1 |
| Throw Type | Double Throw | Amperage | 20 A |
| Number of Poles | Single Pole | Requires Neutral Wire | Yes |
| Indoor/Outdoor | Indoor | Mounting Type | Wall Box |
| Wire Connection Type | Screw Terminals | Voltage | 120 VAC, 277 VAC |
| Load Type | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon | | |