



**Pass and Seymour**  
**Turnlok® Portable 2-Foot In-Line 15A Self-Test GFCI with Plug and Connector, Manual Reset**  
Part No. 1597TL2M



The perfect option for safely powering portable equipment, outdoors or in, when a GFCI-protected outlet is not accessible. Use this 2-Foot In-Line Portable GFCI (Manual Reset) when plugging in drills, saws, leaf blowers, pressure washers, power painters, etc. for protection against electrical shock caused by ground-faults.

Designed with Legrand's Turnlok connector to lock plugs in place, preventing accidental disconnection for safer, more reliable operation.

GFCI protection is required by code in bathrooms, kitchens, garages, outdoor areas, and for any other outlets found within six feet of a sink or water source.

## Features & Benefits

Protects against electrical shock caused by ground-fault occurrences.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected. Open neutral relay automatically cuts power to device line conductor if the neutral wire preceding the portable GFCI becomes damaged.

Conducts an industry-leading automatic self-test every 3 seconds. If the portable GFCI device ever fails, the red indicator light flashes to signal it should be replaced.

Requires portable GFCI to be manually set for use by pressing reset button upon plug in and after loss of primary power.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
Finish	Matte	Country Of Origin	China
Outlet Type	GFCI	Application Sector	Residential/Commercial
Warranty Type	1-Year Limited Warranty		

### Dimensions

Product Width US	2.0 in	Product Weight US	1.0 lb
Product Depth US	1.75 in	Product Length US	27.75 in

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	943	cULus Listed	Yes
---------------------	-----	--------------	-----

---

### Additional Information

---

RoHS Conformant                      Yes

---

### Technical Information

---

Is Tamper-Resistant                  No                                      Amperage                                  15 A

---

Is Weather Resistant                  No                                      Indoor/Outdoor                          Outdoor

---

NEMA Configuration Code              5-15P, 5-15R                          Voltage                                      125.0 V

---